


Screw-in plug to DIN 3852-1 Type A



3 Type

- A without gasket
- AC with gasket in copper
- AA with gasket in aluminum

2

d ₁		d ₂ h14	d ₃	d ₄	l ₁ ±0,2	l ₂ +0,5	s	A/F
metr. thread	Tube thread			Gasket Outside-Ø				
M 8 x 1	-	12	8,3	11,5	8	3	1	4
M 10 x 1	-	14	10,3	13,5	8	3	1	5
-	G 1/8	14	10	13,5	8	3	1	5
M 12 x 1,5	-	17	12,3	16	12	3	1,5	6
-	G 1/4	18	13,4	18	12	3	1,5	6
M 14 x 1,5	-	19	14,3	18	12	3	1,5	6
M 16 x 1,5	-	21	16,3	20	12	3	1,5	8
-	G 3/8	22	17	21	12	3	1,5	8
M 18 x 1,5	-	23	18,3	22	12	4	1,5	8
M 20 x 1,5	-	25	20,3	24	14	4	1,5	10
-	G 1/2	26	21,3	26	14	4	1,5	10
M 22 x 1,5	-	27	22,3	27	14	4	1,5	10
M 24 x 1,5	-	29	24,3	29	14	4	2	12
M 26 x 1,5	-	31	26,3	31	16	4	2	12
M 27 x 2	-	32	27,3	32	16	4	2	12
-	G 3/4	32	26,7	32	16	4	2	12
M 30 x 1,5	-	36	30,3	36	16	4	2	17
M 33 x 2	-	39	33,3	39	16	5	2	17
-	G 1	39	33,5	39	16	5	2	17
M 42 x 2	-	49	42,3	49	16	5	2	22
-	G 1 1/4	49	42,2	49	16	5	2	22
M 48 x 2	-	55	48,3	55	16	5	2	24
-	G 1 1/2	55	48,1	55	16	5	2	24

Specification

- Steel
- Tensile strength class 5.8
- ultrasonically and tensile tested
- zinc plated, nano-passivated
- Strength values of screws → Page 1481
- RoHS compliant

On request

- Stainless Steel version (NI)

1

ST

Information

The gaskets in types AC and AA correspond to the gaskets DIN 7603, type A (flat gaskets).

see also...

- Threaded plugs GN 749 (with rubber seal) → Page 1115

How to order

DIN 908-ST-M24x1,5-A

- 1 Material
- 2 d₁
- 3 Type

