



1 2

d ₁	l ₁ Nominal length									d ₂ MS pivot	d ₃ KU pivot	l ₂ MS pivot	l ₃ KU pivot	A/F
	3	4	5	6	8	10	-	-	-					
M 3	3	4	5	6	8	10	-	-	1,9	1,5	0,5	0,8	1,5	
M 4	4	-	-	-	-	-	-	-	2,5	2	0,5	1,2	1,5	
M 4	5	-	-	-	-	-	-	-	2,5	2	0,5	1	1,5	
M 4	6	8	10	12	16	-	-	-	2,5	2	0,5	1	2	
M 5	5	6	-	-	-	-	-	-	3	3	0,5	1	2	
M 5	8	10	12	16	20	-	-	-	3	3	0,5	1	2,5	
M 6	6	8	10	12	16	20	25	32	4	3,5	1	1,3	3	
M 8	8	10	12	16	20	25	32	40	6	5	1,5	1,6	4	
M 10	16	20	25	32	40	50	-	-	8	6,5	2	1,9	5	
M 12	20	25	32	40	50	63	-	-	10	8	2	2,1	6	

Specification

- Screw
Stainless Steel AISI 303
- Thrust pivot
 - Brass **MS**
 - Plastic (Polyacetal POM) **KU**
- Stainless Steel characteristics → Page 1489
- Plastic characteristics → Page 1483
- RoHS compliant

3

Information

Stainless Steel-Grub screws GN 913.5 with pivots in brass or plastic are used in applications, where marks and damage on the workpiece are unacceptable.

see also...

- Stainless Steel-Ball point screws GN 605 (with flat ball) → Page 783

How to order

GN913.5-M6-20-KU

1	d ₁
2	l ₁
3	Thrust pivot

