





ROSTFREI
Inox
Stainless
Steel

Inch
sizes
available

4 Type

- A with adjustable Stainless Steel-Contact plate
- B with fix Stainless Steel-Contact plate

1 2 2 3

l ₁		d ₁		d ₂		l ₂ in clamping position					b	d ₃	d ₄	d ₅	h Stroke at 90° lever movement	l ₃ in clamping position min. max.		l ₄ Adjus- table range	l ₅ in clam- ping position	l ₆ in clam- ping position	t useable thread length
63	M 5	M 5	M 5	16	20	25	30	35	40	50	16	16	19	18,5	0,75	16,3	18,8	2,5	3	16,3	10
63	M 6	M 6	M 6	16	20	25	30	35	40	50	16	16	19	18,5	0,75	16,3	18,8	2,5	3	16,3	10
82	M 6	M 6	M 6	20	25	30	35	40	50	60	20	20	25	22,5	1	19,5	22,5	3	3,7	19,5	12
82	M 8	M 8	M 8	20	25	30	35	40	50	60	20	20	25	22,5	1	19,5	22,5	3	3,7	19,5	12
101	M 8	M 8	M 8	20	25	30	35	40	50	60	25	26	30	27	1,5	25,3	29,3	4	4,8	25,3	15
101	M 10	M 10	M 10	20	25	30	35	40	50	60	25	26	30	27	1,5	25,3	29,3	4	4,8	25,3	15

Ausführung

- Lever
Stainless Steel AISI CF-8
- Axis, lag nut / screw
setting nut / screw
Stainless Steel AISI 303
- Contact plates
Stainless Steel
- AISI 431
- hardened
- RoHS compliant

On request

- Clamping surface free of grease

Hinweis

Stainless Steel-Clamping levers with eccentrical cam GN 927.7 are used for rapid clamping and releasing. Hereby, contrary to a clamping operation via a thread, these levers permit a **torque-free** clamping.

The lever has been designed to ensure that its movement cannot exceed the max. clamping force.

There are no loose components since they are all assembled and mounted in their correct order.

Type A has the following benefits:

The distance between the lever cam and the clamping surface is adjustable via a fine pitch thread, allowing the clamping position to be set easily with maximum clamping force. Also, the position of the lever relative to the clamping axis can be determined.

With these clamping levers with eccentrical cam GN 927.7, clamping forces of up to 8 kN can be reached.

Clamping levers with eccentrical cam, with internal thread		1	l ₁
GN 927.7-63-M6-A		2	d ₁
		3	Type

Clamping levers with eccentrical cam, with screw		1	l ₁
GN 927.7-82-M8-25-A		2	d ₂
		3	l ₂
		4	Type