



2 Type

- T4** with U-bolt latch, with catch
- T** without U-bolt latch, with catch

1

Size	F_H in N Holding capacity	a	b_1	b_2	b_3	b_4	b_5	d_1	d_2	$h_1 \approx$	h_2
160	1600	5	26	35	21	25,5	14	M 4	4,3	40	10
320	3200	8	36	44	32	37	22	M 6	6,5	57,5	15
700	7000	13	52	54	38	48,5	26	M 8	8,5	82	23

Size	$l_1 \approx$	l_2 min.	m_1	m_2	m_3	m_4	m_5	$r \approx$ at $w_2 = 0$	s	w_1 Stroke	$w_2 \approx$ Adjustable range
160	104	4,5	22	6,5	13	6,5	14,3	50	2	32	12
320	159	6	25,5	8,5	19	10,5	20,5	78	3	53	21
700	225	8	36,5	10	32	13,5	27	98	3,5	64	30

Specification

- Parts in sheet metal
Case-hardened steel C10
zinc plated, blue passivated
- U-bolt latch
Steel St. 37
zinc plated, blue passivated
- All moving parts
lubricated with special grease
- Handle with plastic sleeve
red, oil resistant
- **RoHS compliant**

Information

The stroke of the U-bolt latch of GN 851.2 latch type toggle clamps can be adjusted within its range.

In the clamped position the U-bolt latch and the clamping arm are horizontal to the vertical fixing plane.

In addition to the standard lengths of the U-bolt latches shown in the table, a variety of other lengths are also available under the GN 951.1 series.

see also...

- *General information for toggle clamps* → Page 500
- *Square U-bolts GN 951.1* → Page 560

How to order

GN851.2-160-T4

1 Size

2 Type