



**4 Type**

**A** front rounded, long version

1 2 3

b h9	h	Length l																	for shaft-Ø		
																				from	to
2	2	6	8	10	12	14	16	18	20	-	-	-	-	-	-	-	-	-	-	6...	8
3	3	6	8	10	12	14	16	18	20	22	25	28	30	32	35	36	-	-	-	8...	10
4	4	6	8	10	12	14	16	18	20	22	25	28	32	36	40	45	-	-	-	10...	12
5	5	8	10	12	14	16	18	20	22	25	28	32	36	40	45	50	-	-	-	12...	17
6	6	12	14	16	18	20	22	25	28	32	36	40	45	50	56	63	-	-	-	17...	22
8	7	12	14	16	18	20	22	25	28	32	36	40	45	50	56	63	70	80	90	22...	30
10	8	16	18	20	22	25	28	32	36	40	45	50	56	63	70	80	90	100	110	30...	38
12	8	20	25	28	32	36	40	45	50	56	63	70	80	90	100	125	-	-	-	38...	44

**Specification**

- Steel C45+C blank
- ISO-Fundamental tolerances → Page 1479
- RoHS compliant

**On request**

- b = 14, 16, 18, 20

**Information**

Keys DIN 6885 are only in packing units of 50 pieces for each size and length available.

see also...

- Keyway type in the bore and the shaft → Page 1420

How to order

1 2 3 4  
**DIN 6885-6-6-28-A**

1	b
2	h
3	Length l
4	Type