



Type A



Type C



5 Type

- A without bores
- C with bores and slotted holes

<sup>2</sup> h <sub>1</sub>	<sup>3</sup> b <sub>1</sub>	<sup>4</sup> l <sub>1</sub>	b <sub>3</sub>	d	h <sub>2</sub>	l <sub>2</sub>	m <sub>1</sub>	m <sub>2</sub>	s
30	45	30	18	6,2	18	15	-	20	4
30	45	60	18	6,2	18	15	30	20	4
40	60	40	24	8,2	24	20	-	25	5
40	60	80	24	8,2	24	20	40	25	5
50*	75	50	30	10,2	30	25	-	30	6
50*	75	100	30	10,2	30	25	50	30	6

\* only available in version ALM

Specification

- Structural Steel drawn, with sharp edges blackened
- Aluminum pressed matt, ground
- RoHS compliant

<sup>1</sup> Information

**STB** GN 970 installation brackets are used universally for right-angle connecting and fastening of, e.g. base plates or covers.

**ALM** Type A allows for the use of drilling templates specific to the application as well as fastening by welding.

Type C installation brackets have one or two combinations of a hole and an elongated hole depending on the length l<sub>1</sub>.

see also...

- Angle pieces, Shackles GN 967 → New products

How to order

1	Material
2	h <sub>1</sub>
3	b <sub>1</sub>
4	l <sub>1</sub>
5	Type

<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup> <sup>5</sup>  
GN970-STB-40-40-80-A

