


**Rost frei** Inox Stainless Steel

- 3 Type**
- A** Thread for fixing from the back
  - B** Through-hole for fixing from the operators side
  - C** Fixed from the operators side by means of welding

- 4 Identification no.**
- 1** Handle 90° foldaway
  - 2** Handle 90° foldaway, with retaining spring
  - 3** Handle 180° foldaway
  - 4** Handle 180° foldaway, with retaining spring



Length l	b <sub>1</sub>	b <sub>2</sub>	b <sub>3</sub>	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub> ≈	h <sub>3</sub>	h <sub>4</sub>	m	t <sub>1</sub>	t <sub>2</sub>
120	124	20	106	M 6	6,4	16	53	49	59	60	10	9,6

**Specification**

- Attachment part  
Stainless Steel precision casting  
AISI CF-8 **NI**  
- matte shot-blasted **GS**  
- plastic coated  
(only type A and B)  
black, RAL 9005, textured finish **SW**
- Handle  
Stainless Steel  
AISI 304  
matte shot-blasted
- Retaining springs  
spring steel  
AISI 301
- Load rating information → Page XYZ
- Stainless Steel characteristics → Page 1489
- RoHS compliant

**Information**

GN 425.9 Stainless Steel-Folding handles are used where the handle must only protrude a short distance in the resting position.

Folding handles numbers 1 and 2 are suitable for side “access,” as these have a 90° limit stop. If used from above, numbers 3 and 4 with a handle which can fold freely through 180° are a better version.

The retaining springs of numbers 2 and 4 keep the handle in any position. This keeps the handle in a position which can be easily accessed and prevents noise as a result of vibration in the resting position.

The handle and the retaining springs are secured by mounting the attachment across the entire surface. All components are supplied unassembled.

see also...

- Folding handles GN 425.8 (with recessed tray) → Page 124

How to order	1 Length l
	2 Material
	3 Type
	4 Identification no.
	5 Finish

**GN 425.9-120-NI-A-1-SW**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4