



Inch sizes available

1 l_1	2 d_1 Thread			2 d_2 H7 Bore		d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
22	M 3	M 4	M 5	-	-	8	10,5	18,5	2	23	3	5
30	M 3	-	-	-	-	10	13	24,5	4	31	3,5	7
30	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	31	3,5	8
45	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	34	3,5	8
63	M 6	M 8	-	B 8	-	13,5	17,5	31	6,5	45	4	11
78	M 8	M 10	M 12	B 8	B 10	16	21	36	8	54	4	14
92	M 10	M 12	-	B 12	-	19	24	43	11	64	4	17
108	M 12	M 16	-	B 12	B 16	23	30	50,5	12	75	5	22

Specification

- Handle
Zinc die casting
- plastic coated
black, RAL 9005, textured finish
black, RAL 9011, silk finish
orange, RAL 2004, textured finish
red, RAL 3000, textured finish
silver, RAL 9006, textured finish
- chrome-plated
- uncoated
slide grinded
- Bushing and retaining screw
Stainless Steel AISI 303
- ISO-Fundamental tolerances → Page 1479
- Stainless Steel characteristics → Page 1489
- RoHS compliant

- **SW**
- **SZ**
- **OS**
- **RS**
- **SR**
- **CR**
- **RH**

Information

Adjustable hand levers GN 300.1 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

- Adjustable hand levers GN 300 (bushing steel) → Page 318
- Adjustable Stainless Steel-Hand levers GN 300.5 (matte shot-blasted) → Page 325
- Adjustable hand levers GN 303.1 (with push button) → Page 330

How to order

GN300.1-78-M10-OS

1	l_1
2	d_1
3	Color (Finish)