




ROSTFREI  
Inox  
Stainless  
Steel


**4 Type**

- B** with plain washer
- E** with washer with eyelet
- L** with washer with mounting shackle (only identification no. 1)




**5 Identification no.**

- 1** without cross hole
- 2** with cross hole for spring cotter pin GN 1024



Spring cotter pin  
GN 1024



| <b>2</b>                | <b>3</b>             |    |    |     |    |     | <b>d<sub>2</sub></b> | <b>d<sub>3</sub></b> | <b>d<sub>4</sub></b> | <b>d<sub>5</sub></b> | <b>l<sub>2</sub></b> | <b>l<sub>3</sub></b> | <b>l<sub>4</sub></b> | <b>l<sub>5</sub></b> | <b>l<sub>6</sub></b> |
|-------------------------|----------------------|----|----|-----|----|-----|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|
| <b>d<sub>1</sub> h9</b> | <b>l<sub>1</sub></b> |    |    |     |    |     |                      |                      |                      |                      |                      |                      |                      |                      |                      |
| 8                       | 16                   | 20 | 24 | 28  | 30 | 32  | 2,5                  | 12                   | 2,5                  | 4,3                  | 5,5                  | 7                    | 13,5                 | 18                   | 10                   |
| 8                       | 35                   | 40 | 45 | 50  | 55 | 60  | 2,5                  | 12                   | 2,5                  | 4,3                  | 5,5                  | 7                    | 13,5                 | 18                   | 10                   |
| 10                      | 20                   | 24 | 30 | 35  | 40 | 45  | 2,5                  | 15                   | 2,5                  | 4,3                  | 6                    | 7                    | 15                   | 21                   | 11                   |
| 10                      | 50                   | 55 | 60 | 65  | 70 | 80  | 2,5                  | 15                   | 2,5                  | 4,3                  | 6                    | 7                    | 15                   | 21                   | 11                   |
| 12                      | 20                   | 24 | 30 | 35  | 40 | 45  | 2,5                  | 17                   | 3                    | 5,3                  | 7                    | 9                    | 18,5                 | 23                   | 12                   |
| 12                      | 50                   | 55 | 60 | 65  | 70 | 80  | 2,5                  | 17                   | 3                    | 5,3                  | 7                    | 9                    | 18,5                 | 23                   | 12                   |
| 16                      | 32                   | 35 | 40 | 45  | 50 | 55  | 3,5                  | 22                   | 3                    | 5,3                  | 8                    | 9                    | 21                   | 28                   | 15                   |
| 16                      | 60                   | 65 | 70 | 80  | 90 | 100 | 3,5                  | 22                   | 3                    | 5,3                  | 8                    | 9                    | 21                   | 28                   | 15                   |
| 20                      | 40                   | 45 | 50 | 55  | 60 | 65  | 4,5                  | 26                   | 3,5                  | 6,4                  | 10,5                 | 9                    | 24                   | 31                   | 17                   |
| 20                      | 70                   | 80 | 90 | 100 | -  | -   | 4,5                  | 26                   | 3,5                  | 6,4                  | 10,5                 | 9                    | 24                   | 31                   | 17                   |

| <b>2</b>                | <b>3</b>             |    |    |     |    |     | <b>l<sub>7</sub></b> | <b>s<sub>1</sub></b> | <b>s<sub>2</sub></b> | suitable key rings for identification no. 2 |  | suitable spring cotter pins for identification no. 2 |  |
|-------------------------|----------------------|----|----|-----|----|-----|----------------------|----------------------|----------------------|---|--|--|--|
| <b>d<sub>1</sub> h9</b> | <b>l<sub>1</sub></b> |    |    |     |    |     |                      |                      |                      |   |  |  |  |
| 8                       | 16                   | 20 | 24 | 28  | 30 | 32  | 2                    | 3                    | 4                    | Ø14   |  | GN 1024-NI-2-D                                       |  |
| 8                       | 35                   | 40 | 45 | 50  | 55 | 60  | 2                    | 3                    | 4                    | Ø14   |  | GN 1024-NI-2-D                                       |  |
| 10                      | 20                   | 24 | 30 | 35  | 40 | 45  | 4                    | 3                    | 4                    | Ø14   |  | GN 1024-NI-2-E / ...-D                               |  |
| 10                      | 50                   | 55 | 60 | 65  | 70 | 80  | 4                    | 3                    | 4                    | Ø14   |  | GN 1024-NI-2-E / ...-D                               |  |
| 12                      | 20                   | 24 | 30 | 35  | 40 | 45  | 4                    | 4                    | 4,5                  | Ø14 / Ø18                                   |  | GN 1024-NI-2-E / ...-D                               |  |
| 12                      | 50                   | 55 | 60 | 65  | 70 | 80  | 4                    | 4                    | 4,5                  | Ø14 / Ø18                                   |  | GN 1024-NI-2-E / ...-D                               |  |
| 16                      | 32                   | 35 | 40 | 45  | 50 | 55  | 6                    | 4                    | 4,5                  | Ø14 / Ø18                                   |  | GN 1024-NI-3-E / ...-D                               |  |
| 16                      | 60                   | 65 | 70 | 80  | 90 | 100 | 6                    | 4                    | 4,5                  | Ø14 / Ø18                                   |  | GN 1024-NI-3-E / ...-D                               |  |
| 20                      | 40                   | 45 | 50 | 55  | 60 | 65  | 6                    | 4                    | 5                    | Ø14 / Ø18 / Ø24                             |  | GN 1024-NI-4-E / ...-D                               |  |
| 20                      | 70                   | 80 | 90 | 100 | -  | -   | 6                    | 4                    | 5                    | Ø14 / Ø18 / Ø24                             |  | GN 1024-NI-4-E / ...-D                               |  |