


2 Bore code
B without keyway
K with keyway

1 3							
d ₁	d ₂ H7 Bore			d ₃	b	l ₁	l ₂ ≈
80	10	12	-	26	14	16	29
100	10	12	-	28	15	17	33
125	12	14	-	31	16	18	36
160	14	16	-	36	18	20	40
200	18	20	22	42	22	24	45
250	22	24	26	48	26	28	50
315	26	28	30	56	28	33	56
400	30	32	-	65	32	38	63

Specification

- Aluminum
 - Hub machined
 - Rim turned and polished
 - Unmachined body shot-blasted
- Rim concentric and square to bore < 0,4
- Keyway P9 DIN 6885 → Page 1420
- Cross holes GN 110 → Page 1422
- ISO-Fundamental tolerances → Page 1479
- RoHS compliant

Information

Disc handwheels DIN 3670 have recessed grips at their back. As a rule they are supplied without handle, but the mounting of a handle is possible.

The handwheel diameter d₁=80 and d₁=400 are not provided in the official standard sheet.

see also...

- Countersunk washers GN 184 (for axial fixing) → Page 814

How to order		1	d ₁
DIN 3670-125-K12		2	Bore code
		3	d ₂