



- 1 Type**
- ST** Plastic (KT)
Technopolymer (Polyamide PA)
 - SK** Plastic (KU)
Duroplast (PF)

d ₁	d ₂	Length l ≈ GN 6336.4														Length l ≈ GN 6336.5														d ₃	h ₁	h ₂
		Type ST														Type SK																
25	M 5	10	15	20	25	30	-	-	-	-	-	-	-	-	-	10	15	20	25	30	12	16	8									
25	M 6	10	16	20	25	30	35	45	60	-	-	-	-	-	-	10	16	20	25	30	12	16	8									
32	M 6	10	16	20	25	30	35	45	60	16	20	25	30	35	45	10	16	20	25	30	14	20	10									
32	M 8	16	20	25	30	35	40	50	55	-	-	-	-	-	-	20	25	30	40	-	14	20	10									
40	M 8	16	20	25	30	35	40	50	55	16	20	25	30	40	55	20	25	30	40	-	18	25	13									
40	M 10	15	20	25	30	35	40	45	55	-	-	-	-	-	-	20	25	30	45	55	18	25	13									
50	M 10	15	20	25	30	35	40	45	55	25	30	35	45	55	-	20	25	30	45	55	22	32	17									
50	M 12	20	25	30	35	40	50	60	-	-	-	-	-	-	-	30	40	50	-	-	22	32	17									
63	M 12	20	25	30	35	40	50	60	-	30	35	40	50	60	-	30	40	50	-	-	26	40	21									
80	M 16	-	-	-	-	-	-	-	-	30	40	50	60	70	-	-	-	-	-	-	35	50	25									

Specification

- **GN 6336.4**
 - Threaded stud
Steel
zinc plated, blue passivated
 - Knob (Type ST)
Technopolymer (Polyamide PA)
shock-resistant, black matte
 - Knob (Type SK)
Duroplast, black shiny

- **GN 6336.5**
 - Threaded stud
Stainless Steel
M6... M10: AISI 304 Cu
M12: AISI 303
 - Knob (Type ST)
Technopolymer (Polyamide PA)
shock-resistant, black matte

- Plastic characteristics → Page 1483
- Stainless Steel characteristics → Page 1489
- RoHS compliant

Information

Star knobs GN 6336.4 / GN 6336.5 comply with DIN 6336 type L.

see also...

- Star knobs GN 6336.10 (with brass / plastic pivot) → Page 402
- Star knobs GN 6336.12 (with movable thrust pad) → Page 403
- Star knobs GN 6336.13 (with loss protection) → Page 405

How to order (Threaded stud steel)

GN 6336.4-SK-32-M6-25

- | | |
|---|----------------|
| 1 | Type |
| 2 | d ₁ |
| 3 | d ₂ |
| 4 | Length l |

How to order (Threaded stud Stainless Steel)

GN 6336.5-ST-63-M12-60

- | | |
|---|----------------|
| 1 | Type |
| 2 | d ₁ |
| 3 | d ₂ |
| 4 | Length l |