



- 4 Type**
- A** with cylindrical bore
 - B** with bore for countersunk screw

| 2 d_1 <small>+0,5 +0,2</small> | 3 d_2 | | d_3 Type B | s |
|---|-------------------|----|-----------------|-----|
| 4 | 10 | 13 | 8,4 | 2,5 |
| 5 | 13 | 16 | 10,5 | 3 |
| 6 | 15 | 20 | 12,6 | 4 |
| 8 | 20 | 26 | 16,8 | 5 |
| 10 | 25 | 32 | 21 | 6,5 |
| 12 | 30 | 40 | 25,2 | 7,5 |

Specification

- Steel **ST**
 - turned **BT**
 - zinc plated, blue passivated **ZB**
- Stainless Steel AISI 303 **NI**
 - turned **MT**
 - matt shot-blasted
- Stainless Steel characteristics → Page 1489
- RoHS compliant

Information

Washers GN 6341 are used mainly in mechanical machine and jig construction when DIN 125, DIN 9021 and DIN 6340 washers no longer meet requirements.

In particular, Type B for countersunk screws is ideal for solid screw connections with a low construction height.

see also...

- Heavy duty washers GN 6339 → Page 812
- Countersunk washers GN 184 → Page 814
- Washers DIN 6340 → Page 816

| | |
|--------------|---------------------------|
| How to order | 1 Material |
| | 2 d_1 |
| | 3 d_2 |
| | 4 Type |
| | 5 Finish |

GN6341-ST-8-26-B-ZB