



1 Type
TE Plastic Technopolymer (Polyamide PA)

2 d ₁	3 d ₂	4 Length l ≈									d ₄	h ₁	h ₂	h ₃
25	M 5	10 15 20	-	-	-	-	-	-	-	-	10	16	8	6
32	M 6	16 20 25	30	35	45	-	-	-	-	-	12	20	10	8,5
40	M 8	16 20 25	30	35	40	45	55	-	-	-	14	26	13	10
50	M 10	25 30 35	45	55	-	-	-	-	-	-	18	32	17	10
63	M 12	30 35 40	50	60	-	-	-	-	-	-	20	40	21	14

Specification

- Knob (Type ST) Technopolymer (Polyamide PA)
 - shock-resistant
 - black, matte finish
- **GN 6336.4** Threaded stud Steel zinc plated, blue passivated
- **GN 6336.5** Threaded stud Stainless Steel AISI 303
- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- **RoHS compliant**

Information

The star knobs have an immaculate contact or clamping surface thanks to the protruding steel / Stainless Steel bushing.

see also...

- *Star knobs 6336.4 (without protruding bushing, threaded stud steel) → Page 399*
- *Star knobs 6336.5 (without protruding bushing, threaded stud Stainless Steel) → Page 399*

How to order (Threaded stud steel)

GN 6336.4-TE-50-M10-30

1	Type
2	d ₁
3	d ₂
4	Length l

How to order (Threaded stud Stainless Steel)

GN 6336.5-TE-40-M8-16

1	Type
2	d ₁
3	d ₂
4	Length l