



1 Type


- Operation with
- DK** triangular spindle (DK7)
- VK7** square spindle A/F7
- VK8** square spindle A/F8
- SCH** slot
- VDE** double bit
- SK10** hexagon A/F10




Type DK




Type VK7 / VK8



Type SK10



Type SCH



Type VDE

2

Latch distance A											d	h
4	8	13	16	20	24	28	32	36	40	45	28	4
6	10	14	18	22	26	30	34	38	42	50	28	4

Specification

- Lock housing
Zinc die casting
- Locating ring
 - chrome plated (Standard) —
 - plastic coated
black, RAL 9005, textured finish ● SW
- All other parts
Steel zinc plated, blue passivated
- RoHS compliant

Accessories

- Socket keys GN 119.2 → Page 940
- Protective caps GN 120 → Page 942
- Opening handles GN 120.1 → Page 943

3

Information

Latches GN 115 lock by a turning operation limited to 90° which moves the locking behind the door frame. The bevels of the latch ease the closing of the door.

Latches with different cranks cover a latch distance A from 4 to 50 mm.

Latches GN 115 are supplied with loosely enclosed latch.

see also...

- Construction and assembly instructions → Page 897
- List of latch types → Page 892 ff.
- Latches GN 115 (operation with operating elements) → Page 899
- Stainless Steel-Latches GN 115 (operation with key) → Page 902

How to order (chrome plated locating ring)

1	Type
2	Latch distance A

How to order (black locating ring)

1	Type
2	Latch distance A
3	Finish