



ROSTFREI
Inox
Stainless
Steel

1		2										
d ₁	Length l								d ₂	d ₃	h	k
M 2	4	6	8	10	-	-	-	-	9	4,5	5,3	2
M 2,5	4	6	8	10	12	-	-	-	11	5	6,5	2,5
M 3	6	8	10	12	16	20	-	-	12	6	7,5	2,5
M 4	5	8	10	12	16	20	25	-	16	8	9,5	3,5
M 5	6	8	10	12	16	20	25	30	20	10	11,5	4
M 6	8	10	12	16	20	25	30	35	24	12	15	5
M 8	12	16	20	25	30	35	40	-	30	16	18	6
M 10	12	15	20	25	30	35	40	-	36	20	23	8

Specification

- Steel
 - Tensile strength class 5.8
 - visible face fine turned
 - blackened
 - zinc plated, blue passivated
- Stainless Steel AISI 303
- Stainless Steel characteristics → Page 1489
- Strength values of screws → Page 1481
- RoHS compliant

Information

- Knurled screws DIN 464 are machined from solid bar.
- Unlike in the official standard sheet, they are generally made with thread right up to the head and without recess groove at the end of the thread.
- The official standard sheet also provides for the sizes M1 / M1,2 and M1,6.
- see also...
- Flat knurled screws DIN 653 → Page 459
 - Knurled screws GN 653.2 (with recessed stud for loss protection) → Page 461
 - Stainless Steel-Knurled screws GN 535 → Page 452
 - Knurled screws DIN 464 with loss protection GN 111.7 → Page 1426

How to order (Steel, blackened)	1	d ₁
	2	Length l

How to order (Steel, zinc plated)	1	d ₁
	2	Length l
	3	Finish

How to order (Stainless Steel)	1	d ₁
	2	Length l
	3	Material