





Type A0





Type A1



Type A3



Type B0



4 Type (Base plate)

- A0** without rubber underlay
B0 without rubber underlay, with 2 mounting holes
A1 with rubber underlay, clipped on, black
A3 with rubber underlay, rubber vulcanised, black

1	2	3											3					
d ₁	d ₂	l ₁									l ₇ Vers. X	d ₃	h ₁	h ₆	m	s		
			Version S / SK				Version U / UK											
40	M 8	40	50	63	-	-	-	-	-	-	25	5,4	2	3,5	30	1,5		
40	M 10	50	60	80	100	-	-	-	-	-	28	5,4	2	3,5	30	1,5		
40	M 12	60	80	100	125	-	-	-	-	-	31	5,4	2	3,5	30	1,5		
40*	M 16	-	-	-	-	75	100	125	150	200	37	5,4	2	3,5	30	1,5		
50	M 8	40	50	63	-	-	-	-	-	-	25	6,6	2,5	4	38	2		
50	M 10	50	60	80	100	-	-	-	-	-	28	6,6	2,5	4	38	2		
50	M 12	60	80	100	125	-	-	-	-	-	32	6,6	2,5	4	38	2		
50	M 16	-	-	-	-	75	100	125	150	200	37	6,6	2,5	4	38	2		
60	M 8	40	50	63	-	-	-	-	-	-	25	6,6	2,5	4,5	48	2		
60	M 10	50	60	80	100	-	-	-	-	-	28	6,6	2,5	4,5	48	2		
60	M 12	60	80	100	125	-	-	-	-	-	32	6,6	2,5	4,5	48	2		
60	M 16	-	-	-	-	75	100	125	150	200	37	6,6	2,5	4,5	48	2		
80	M 8	40	50	63	-	-	-	-	-	-	26	8,6	3	5	64	2		
80	M 10	50	60	80	100	-	-	-	-	-	29	8,6	3	5	64	2		
80	M 12	60	80	100	125	-	-	-	-	-	32	8,6	3	5	64	2		
80	M 16	-	-	-	-	75	100	125	150	200	38	8,6	3	5	64	2		
80	M 20	-	-	-	-	75	100	125	150	200	45	8,6	3	5	64	2		
80	M 24	-	-	-	-	100	125	150	200	-	-	8,6	3	5	64	2		

Specification

* not available in type B0

- Base plate
Steel, zinc plated
- Threaded stem
Steel, zinc plated, blue passivated
- Hexagon nut ISO 4032
Steel, zinc plated, blue passivated

- Rubber underlay, clipped on
black, Santoprene® (TPE)
≈ 80 Shore A
- Rubber underlay, vulcanised
black, Perbunan® (NBR)
70±5 Shore A

- Elastomer characteristics → Page 1483
- Load rating information → Page 1472
- RoHS compliant