



Fastening screws



**2 Type**

**F** with rubber stop, locking device in back, detach function

**3 Identification no.**

**1** Fastening using through-holes

**1**

l <sub>1</sub>	l <sub>2</sub> <sup>+3</sup> / <sub>-3</sub> Stroke	l <sub>3</sub>	F <sub>S</sub> per pair in N	
			at 10,000 cycles	at 100,000 cycles
250	250	500	450	320
300	300	600	460	340
350	350	700	480	360
400	400	800	510	390
450	450	900	510	390
500	500	1000	480	360

**1**

l <sub>1</sub>	l <sub>2</sub> <sup>+3</sup> / <sub>-3</sub> Stroke	l <sub>3</sub>	F <sub>S</sub> per pair in N	
			at 10,000 cycles	at 100,000 cycles
550	550	1100	460	340
600	600	1200	440	340
650	650	1300	420	320
700	700	1400	420	320
750	750	1500	400	300
800	800	1600	400	300

**Specification**

- Slide profile  
Steel, zinc plated, blue passivated **ZB**
- Bearings  
Roller bearing steel, hardened
- Ball cage, outer slide  
Plastic
- Ball cage, inner slide  
Steel, zinc plated
- Rubber stop and detach function  
Plastic / Elastomer
- Operating temperature -20 °C to 100 °C
- RoHS compliant

**On request**

- other lengths and hole spacing
- other attachment options
- other surfaces

**4**

**Information**

Telescopic slides GN 1410 are installed vertically and in pairs. The stroke reaches ≈ 100 % of the nominal length l<sub>1</sub> (full extension).

The telescopic slides are delivered in **pairs**. They can be installed on the extension on either the left or right side due to the mechanics. All mounting holes are easy to reach through auxiliary holes. Only the mounting holes are shown, but other production-related holes may be present.

see also...

- Technical information on telescopic slides → Page 44 ff.
- Stainless Steel-Telescopic slides GN 1450 (with full extension) → Page 36
- Telescopic slides GN 1412 (with self-retracting mechanism) → Page 15

How to order

**GN 1410-250-F-1-ZB**

1	l <sub>1</sub>
2	Type
3	Identification no.
4	Finish