




Rost frei
Inox
Stainless
Steel

4 Type

- A** without lock nut
B with lock nut

1 d ₁	2 d ₂	3 h ₁ max.	d ₃	d ₄	h ₂ min.	h ₃ Adjustable range	h ₄ min.	h ₅ Adjustable range	Static load F in kN		Code no. C-Spanner
									ST	NI	
40	79	M 10	69	M 28 x 1,5	40	53	16	59	100	70	DIN 1810-A40-42
40	79	M 10	86	M 28 x 1,5	40	62	24	68	100	70	DIN 1810-A40-42
52	99	M 12	80	M 36 x 1,5	52	61	19	69	125	85	DIN 1810-A52-55
52	99	M 12	103	M 36 x 1,5	52	73	30	80	125	85	DIN 1810-A52-55
65	119	M 16	112	M 45 x 1,5	65	82	30	90	225	155	DIN 1810-A65-70
65	119	M 16	148	M 45 x 1,5	65	100	48	108	225	155	DIN 1810-A65-70

Specification

- Steel **ST**
zinc plated, blue passivated
- Stainless Steel AISI 304 **NI**
- Stainless Steel characteristics → Page 1489
- RoHS compliant

On request

- C-Spanner DIN 1810
(Code no. see table)

Information

GN 360 levelling sets are used for leveling and to compensate for any slope when setting up machines and systems.

The thread d₂ can also be used as a through-hole for attachment from below. The fine thread d₃ allows precise adjustment and readjustment using a DIN 1810 C-Spanner. A circlip limits the maximum path of adjustment.

see also...

- Levelling sets GN 350 / GN 350.1 → Page 850 / 851
- Levelling sets GN 350.2 / GN 350.5 → Page 852 / 853

How to order		1	d ₁
		2	d ₂
		3	h ₁
		4	Type
		5	Material
GN360-119-M16-148-A-ST			