


2 Type

B with rubber stop

3 Identification no.

2 Fastening using countersunk holes

Fastening screws



1

l_1	$l_2^{+4/-4}$ Stroke	l_3	F_S per pair in N	
			at 10,000 cycles	at 100,000 cycles
500	503	988,5	1140	760
600	607	1192,5	1190	790
700	711	1396,5	1310	870
800	815	1600,5	1380	920

Specification

- Slide profile
Steel, zinc plated, blue passivated **ZB**
- Bearings
Roller bearing steel, hardened
- Ball cage
Steel, zinc plated
- Rubber stop
Plastic / Elastomer
- Operating temperature -20 °C to 100 °C
- RoHS compliant

On request

- other lengths and hole spacing
- other attachment options
- other surfaces
- with support bracket

4

Information

Telescopic slides GN 1426 are installed vertically and in pairs. The special design allows the stroke to achieve $\approx 100\%$ of the nominal length l_1 on both sides (double-sided full extension). Applications such as the double-sided loading of a drawer can be realized in this way. The rubber stops of type B dampen the impact of the slide in the front end positions. If larger static or dynamic loads occur in the direction of extension, they should be absorbed by external stop elements.

The telescopic slides are delivered in **pairs**. They can be installed on the extension on either the left or right side due to the mechanics. All mounting holes are easy to reach through auxiliary holes. Only the fastening holes are shown, but other production-related holes may be present.

see also...

- Technical information on telescopic slides \rightarrow Page 44 ff.
- Telescopic slides GN 1420 (with full extension) \rightarrow Page 18

How to order

GN 1426-800-B-2-ZB

1	l_1
2	Type
3	Identification no.
4	Finish