



Fastening screws



2 Type

B with rubber stop

3 Identification no.

2 Fastening using countersunk holes

1

l ₁	l ₂ ⁺⁴ Stroke	l ₃	F _S per pair in N	
			at 10,000 cycles	at 100,000 cycles
400	400	800	1700	1030
450	450	900	1900	1160
500	500	1000	2120	1250
550	550	1100	2300	1400

1

l ₁	l ₂ ⁺⁴ Stroke	l ₃	F _S per pair in N	
			at 10,000 cycles	at 100,000 cycles
600	600	1200	2300	1450
700	700	1400	2280	1450
800	800	1600	2190	1550

Specification

4

- Slide profile
Steel, zinc plated, blue passivated **ZB**
- Bearings
Roller bearing steel, hardened
- Ball cage
Steel, zinc plated
- Rubber stop
Plastic / Elastomer
- Self-retracting mechanism
Stainless Steel / Plastic
- Operating temperature -20 °C to 100 °C
- RoHS compliant

On request

- other lengths and hole spacing
- other attachment options
- with locking device (front)
- other surfaces
- with support bracket

Information

Telescopic slides with self-retracting mechanism GN 1432 are installed vertically and in pairs. The stroke reaches ≈ 100 % of the nominal length l₁ (full extension).

The telescopic slides are delivered in **pairs**. They can be installed on the extension on either the left or right side due to the mechanics. All mounting holes are easy to reach through auxiliary holes. Only the mounting holes are shown, but other production-related holes may be present.

see also...

- Technical information on telescopic slides → Page 44 ff.
- Telescopic slides GN 1422 (with self-retracting mechanism) → Page 20
- Telescopic slides GN 1424 (with dampened self-retracting mechanism) → Page 23

How to order

GN 1432-550-B-2-ZB

- 1 l₁
- 2 Type
- 3 Identification no.
- 4 Finish