




螺桿頭部專利圓弧設計，提供4°萬向自動調整完全水平，使機器及設備平穩度更佳。

Patent pending on the curve design of the bolt ends provides 4 degrees swivel adjustment which eliminate the angle tolerance and makes the machines and devices more stable.



M8主體下壓測驗



M16主體下壓測驗

**材質與表面處理**

- 材質-盤座：DK-10合金鋼(SCM)-鍍鋅。  
DS-10不銹鋼(SUS304)-震動亮面。
- 材質-螺桿：DK-10合金鋼(SCM)-鍍鋅。  
DS-10不銹鋼(SUS304)-電解。

**特徵**

- 螺桿與盤座結合處圓弧設計，提供4°萬向自動調整，解決角度公差，使機器及設備平穩度更佳。
- 防銹(DS系列)、耐磨耗、耐腐蝕性、耐熱。

**MATERIAL AND FINISH**

- Material-Base: DK-10 Steel (SCM)-zinc plated.  
DS-10 Stainless steel (SUS304)-Vibration ground.
- Material-Bolt: DK-10 Steel (SCM)-zinc plated.  
DS-10 Stainless steel (SUS304)- Electro Polishing.

**FEATURES**

- The curve of bolt's bottom and base's hole designs is for automatic leveling best.
- Resistance to conductance rust (DS Series), abrasion, resistance to heat and corrosion.

**SPECIFICATIONS:**

Unit:mm

產品編號Item No.		尺寸 Dimensions							荷重 Load Capacity (kgf)	重量Weight(g)	
SCM	SUS304	M	L	ØD	H1	H2	H3	W		SCM	SUS304
DK-1008035A	DS-1008035A	M8*P1.25	35	40	17.8	12.5	6.5	13	130	51	51
DK-1008050A	DS-1008050A		50							55	55
DK-1008075A	DS-1008075A		75							61	61
DK-1010050A	DS-1010050A	M10*P1.5	50	40	18.8	8	17	190	75	75	
DK-1010075A	DS-1010075A		75						85	85	
DK-1010100A	DS-1010100A		100						96	96	
DK-1012035D		M12*P1.75	35	53.5	22.1	15	10	19	390	105	
DK-1012040D			40							108	
DK-1012075D	DS-1012075D		75							136	136
DK-1012100D	DS-1012100D		100							151	151
DK-1012150D	DS-1012150D		150							181	181
DK-1016075H			75							248	
DK-1016100H	DS-1016100H	M16*P2.0	100	73.2	31.7	22	13	24	780	289	289
DK-1016150H	DS-1016150H		150							345	345
DK-1020100H	DS-1020100H		100							412	412
DK-1020150H	DS-1020150H	M20*P2.5	150	33.7	22	16	30	900	499	499	
DK-1020200H			200						572		