



DK-0930110S




DK-0930110B




單支荷重1100Kgf
Load Capacity 1100Kgf / each




與機械組裝時
(When assembling
with the machine.)



與機械組裝完成
(Complete with the
machinery assembly)



水平調整完成後
(After the adjustment
level complete)



使用說明

- 將盤座墊片放在腳座上，再將機械緩緩降下。
(安裝前，機械腳只需鑽洞，請勿攻牙。)
- 螺桿由上側穿過機械腳及盤座墊片鎖入調整盤座中，再由上放入華司和螺帽。
- 用26mm開口扳手轉動調整盤座，調整出機械適當的高度及水平。
- 完成後將上方華司和螺帽鎖緊。
- 透過3吋鉤型扳手將調整盤座下的固定螺帽向下鎖緊，即完成安裝。

User Manual

- Place the level washer on the glide then lower down machine slowly.
(Before the installation, the mechanical foot please do not tapped hole.)
- Insert the bolt through the machine into the glide then place the nut and washer from the top.
- To adjust machine to its height with the handle by the wrench(26mm).
- To tie the nut and washer when the adjustment is done accurately.
- After locking the socket set nut that is under handle with 3" hook wrench, assembly is finished.

材質與表面處理

- 盤座：FC-250 粉體烤漆(砂黑、砂銀)
- 螺桿：S45C 熱處理及磷酸鋁
- 盤墊：CR 合成橡膠(黑)
- 固定螺帽：FCD45 粉體烤漆(砂黑、砂銀)

MATERIAL AND FINISH

- Base: FC-250 Powder coating (Black / Silver)
- Bolt: S45C with heat treatment and coating with Manganese phosphate
- Cushion: Chloroprene Rubber (Black)
- Socket Set Nut: FCD45 Powder coating (Black / Silver)

特徵

- 當作業場所地面傾斜不平時，自動導正水平角度。
- 確保機械精準度，以防止滑動。
- 防止機械於動作時產生過大震動，改善作業場所環境。
- 防止樓層因機械動作時產生共震、引震、噪音。
- 機器安裝時，可有效導正腳座盤墊面全部伏貼地面，穩定機械運轉。
- 機械腳放到盤座上，在容許荷重下壓時，可用開口扳手在每一調整腳順利調整高度及水平。(如右圖所示)
- 防震、防滑、耐磨損、耐油。
- 附加固定螺帽。有無固定螺帽之差異：當機械震動大時建議使用有固定螺帽機型以防止鬆動。

FEATURES

- Automatic adjust the horizontal angle.
- To ensure the precision of machinery in order to prevent from the slipping out.
- To prevent from the vibration and improve the work environment when the machine is on.
- To decrease the vibration between floors when the machine is running.
- To direct the support of machine on the ground correctly when the machine is installed.
- Smoothly adjust the machine height by the open-end wrench, when machine load on the Heavy-Duty Leveling Glide. (please refer to photo right)
- Resistance to shock, slip, abrasion and greasiness.



SPECIFICATION:

形式 Type	產品編號 Item no.	顏色 Color	尺寸 Dimensions				機械腳厚度允許最大值 Max. Thickness of Machine Support	最大調整量 Max. Adjustable Amount	荷重 Load Capacity (kgf)	重量 Weight (kg)
			D	L	H	H1				
含固定螺帽 With socket set nut	DK-0930110	B(黑 Black) S(銀 Silver)	150	110	161	75	55	24	1100	3.8
	DK-0930200			200	251		145			3.9
不含固定螺帽 Without socket set nut	DK-0931110			110	151	65	55			3.6
	DK-0931200			200	241		145			3.7

※Note: Before the installation, the mechanical foot please do not tapped hole.

※注意事項：安裝前，機械腳請勿攻牙。