


MATERIAL

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

STANDARD EXECUTION

Brass boss, threaded pass-through hole.



Code	Description	D	d	h	d1	H	h1	Tube external diameter	Tube internal diameter	Tube thickness	Max. static load* [N]	⚖
320211	NDX.T-20x2-M8	20	M8	5	16	23	5	20	16	2	4000	23
320221	NDX.T-25x2-M8	25	M8	5.5	21	26	5.5	25	21	2	4500	24
320222	NDX.T-25x2-M10	25	M10	5.5	21	26	5.5	25	21	2	4500	24
320231	NDX.T-30x1-M8	30	M8	10	28	31	6	30	28	1	4500	24
320232	NDX.T-30x1-M10	30	M10	10	28	31	6	30	28	1	4500	24
320233	NDX.T-30x1-M12	30	M12	10	28	31	6	30	28	1	4500	24
320234	NDX.T-30x1-M14	30	M14	15	28	31	6	30	28	1	4500	26
320235	NDX.T-30x1-M16	30	M16	15	28	31	6	30	28	1	4500	26
320241	NDX.T-30x1.5-M8	30	M8	10	27	31	6	30	27	1.5	4500	24
320242	NDX.T-30x1.5-M10	30	M10	10	27	31	6	30	27	1.5	4500	24
320243	NDX.T-30x1.5-M12	30	M12	10	27	31	6	30	27	1.5	4500	24
320244	NDX.T-30x1.5-M14	30	M14	15	27	31	6	30	27	1.5	4500	26
320245	NDX.T-30x1.5-M16	30	M16	15	27	31	6	30	27	1.5	4500	26
320251	NDX.T-30x2-M8#	30	M8	10	26	31	6	30	26	2	4500	24
320252	NDX.T-30x2-M10#	30	M10	10	26	31	6	30	26	2	4500	24
320253	NDX.T-30x2-M12#	30	M12	10	26	31	6	30	26	2	4500	24
320254	NDX.T-30x2-M14#	30	M14	15	26	31	6	30	26	2	4500	26
320255	NDX.T-30x2-M16#	30	M16	15	26	31	6	30	26	2	4500	26
320261	NDX.T-30x2.5-M8#	30	M8	10	25	31	6	30	25	2.5	4500	24
320262	NDX.T-30x2.5-M10#	30	M10	10	25	31	6	30	25	2.5	4500	24
320263	NDX.T-30x2.5-M12#	30	M12	10	25	31	6	30	25	2.5	4500	24
320264	NDX.T-30x2.5-M14#	30	M14	15	25	31	6	30	25	2.5	4500	26
320265	NDX.T-30x2.5-M16#	30	M16	15	25	31	6	30	25	2.5	4500	26
320266	NDX.T-32x2-M8	32	M8	10	28	31	6	32	28	2	4500	28
320267	NDX.T-32x2-M10	32	M10	10	28	31	6	32	28	2	4500	28
320268	NDX.T-35x2-M10	35	M10	10	31	31	6	35	31	2	4500	30
320269	NDX.T-35x2-M12	35	M12	10	31	31	6	35	31	2	4500	30
320271	NDX.T-38x1.5-M8	38	M8	10	35	38	8	38	35	1.5	5000	32
320272	NDX.T-38x1.5-M10	38	M10	10	35	38	8	38	35	1.5	5000	32
320273	NDX.T-38x1.5-M12	38	M12	10	35	38	8	38	35	1.5	5000	32
320274	NDX.T-38x1.5-M14	38	M14	15	35	38	8	38	35	1.5	5000	34
320275	NDX.T-38x1.5-M16	38	M16	15	35	38	8	38	35	1.5	5000	34
320282	NDX.T-38x2-M10	38	M10	10	34	38	8	38	34	2	5000	32
320283	NDX.T-38x2-M12	38	M12	10	34	38	8	38	34	2	5000	32
320284	NDX.T-38x2-M14	38	M14	15	34	38	8	38	34	2	5000	34
320285	NDX.T-38x2-M16	38	M16	15	34	38	8	38	34	2	5000	34
320292	NDX.T-38x2.5-M10#	38	M10	10	33	38	8	38	33	2.5	5000	32
320293	NDX.T-38x2.5-M12#	38	M12	10	33	38	8	38	33	2.5	5000	32
320294	NDX.T-38x2.5-M14#	38	M14	15	33	38	8	38	33	2.5	5000	34
320295	NDX.T-38x2.5-M16#	38	M16	15	33	38	8	38	33	2.5	5000	34
320297	NDX.T-40x3-M10	40	M10	10	34	38	7.5	40	34	3	5000	40
320298	NDX.T-40x3-M12	40	M12	10	34	38	7.5	40	34	3	5000	40
320301	NDX.T-42.4x1.5-M8	42	M8	10	39.4	38	8	42.4	39.4	1.5	5000	44
320302	NDX.T-42.4x1.5-M10	42	M10	10	39.4	38	8	42.4	39.4	1.5	5000	44
320303	NDX.T-42.4x1.5-M12	42	M12	10	39.4	38	8	42.4	39.4	1.5	5000	44
320304	NDX.T-42.4x1.5-M14	42	M14	15	39.4	38	8	42.4	39.4	1.5	5000	46
320305	NDX.T-42.4x1.5-M16	42	M16	15	39.4	38	8	42.4	39.4	1.5	5000	46
320306	NDX.T-42.4x1.5-M20	42	M20	20	39.4	38	8	42.4	39.4	1.5	8000	42