



MATERIAL

Polyethylene (PE), RAL 9005 (C9) black colour or RAL 7042 (C34) grey colour, satin finish.

STANDARD EXECUTIONS


- **NIL-Q**: for square tubes.
- **NIL-R**: for rectangular tubes.
- **NIL-T**: for round tubes.

FITTING

Their fitting to the round, square or rectangular section tube or profile ends can be made either by hand or by a mallet.

SPECIAL EXECUTIONS ON REQUEST

RAL 9003 white coloured inserts.



* Complete with colour index, example: 435010-C9 NIL.T-10-C9

C9
RAL9005

C34
RAL7042

NIL.Q

Code	Description	B	h	h1	External	Thickness
435210-*	NIL.Q-10-*	10	12	4	10	0,8+2,5
435212-*	NIL.Q-12-*	12	12	4	12	1+2
435213-*	NIL.Q-13-*	13	12	4	13	0,5+2
435215-*	NIL.Q-15-*	15	11,5	3	15	1+2
435216-*	NIL.Q-16-*	16	11,5	5	16	1+2,5
435218-*	NIL.Q-18-*	18	11,5	5	18	1,5+3
435220-*	NIL.Q-20-*	20	11,5	5	20	1+3
435222-*	NIL.Q-22-*	22	12	5	22	1+3,5
435225-*	NIL.Q-25-*	25	11,5	5	25	1+3
435228-*	NIL.Q-28-*	28	11,5	5	28	1+3
435230-*	NIL.Q-30-*	30	11,5	5	30	1+3
435232-*	NIL.Q-32-*	32	11,5	5	32	1+3,5
435234-*	NIL.Q-34-*	34	14,5	5	34	1+3
435235-*	NIL.Q-35-*	35	11,5	5	35	1+3
435238-*	NIL.Q-38-*	38	14,5	5	38	1+3,5
435240-*	NIL.Q-40-*	40	14,5	5	40	1+3
435245-*	NIL.Q-45-*	45	14,5	5	45	1+3

NIL.Q

Code	Description	B	h	h1	External	Thickness
435250-*	NIL.Q-50-*	50	14,5	5	50	1+2,5
435370-*	NIL.Q-50-2.6-*	50	24	5,5	50	2.6+4
435255-*	NIL.Q-55-*	55	14,5	5	55	2+4,5
435260-*	NIL.Q-60-*	60	15	5	60	1,5+3,5
435265-*	NIL.Q-65-*	65	21	5	65	1+3
435270-*	NIL.Q-70-*	70	22	5	70	2+5
435275-*	NIL.Q-75-*	75	21	6	75	2+4,5
435276-*	NIL.Q-76,2-*	76,2	21	6	76,2	2,5+5
435280-*	NIL.Q-80-*	80	21	6	80	1,5+4
435290-*	NIL.Q-90-*	90	21	6	90	3+5
435295-*	NIL.Q-95-*	95	21,5	6	95	3,5+5,5
435300-*	NIL.Q-100-*	100	21	7	100	1+4
435310-*	NIL.Q-110-*	110	24	6	110	3+5
435320-*	NIL.Q-120-*	120	30	5	120	2,5+6
435340-*	NIL.Q-140-*	140	34	3	140	4+7
435350-*	NIL.Q-150-*	150	28	7	150	5+8