


Nuts for T-slots DIN 508 enhanced

Item description/product images



Description

Material:

Carbon steel grade 10, EN AW-7075 or stainless steel 1.4571.

Version:

Steel tempered (black).


Aluminium and stainless steel bright.

Note:


Aluminium T-slot nuts have steel threaded inserts.

Strength of stainless steel version:

$R_m = 700 \text{ N/mm}^2$, $R_{p0,2} = 450 \text{ N/mm}^2$.



Drawings



Overview of items

Nuts for T-slots to DIN 508 enhanced

Order No.	Main material	Surface finish body	Slot width	B	B1	D	H	H1	L
K0377.05	high carbon steel	tempered (black)	6	10	5,6	M5	8	4	10
K0377.06	high carbon steel	tempered (black)	8	13	7,6	M6	10	6	13
K0377.061	high carbon steel	tempered (black)	10	15	9,6	M6	12	6	15
K0377.08	high carbon steel	tempered (black)	10	15	9,6	M8	12	6	15
K0377.081	high carbon steel	tempered (black)	12	18	11,6	M8	14	7	18
K0377.082	high carbon steel	tempered (black)	14	22	13,6	M8	16	8	22
K0377.10	high carbon steel	tempered (black)	12	18	11,6	M10	14	7	18
K0377.101	high carbon steel	tempered (black)	14	22	13,6	M10	16	8	22
K0377.12	high carbon steel	tempered (black)	14	22	13,6	M12	16	8	22
K0377.121	high carbon steel	tempered (black)	16	25	15,6	M12	18	9	25
K0377.122	high carbon steel	tempered (black)	18	28	17,6	M12	20	10	28
K0377.123	high carbon steel	tempered (black)	20	32	19,6	M12	24	12	32
K0377.124	high carbon steel	tempered (black)	22	35	21,6	M12	28	14	35
K0377.14	high carbon steel	tempered (black)	16	25	15,6	M14	18	9	25