


Indexing plunger with cam lever, steel or stainless steel, Form B

Item description/product images



Description

Material:

Steel version:
Threaded sleeve 1.0718.
Indexing pin 1.0718.

Stainless steel version:

Threaded sleeve 1.4305.
Indexing pin 1.4305.
Handle fibreglass reinforced thermoplastic PPA (high temperature resistant).

Version:

Steel version:
Threaded sleeve, black oxidised.
Indexing pin hardened, ground and black oxidised.

Stainless steel version:

Threaded sleeve, bright.
Indexing pin ground and left bright.

Grip black or traffic red RAL3020.

Note:

Indexing plungers are used where it is necessary to prevent changes of position due to lateral forces. A new locking position can be set only after the plunger has been manually disengaged. With this indexing plunger a cam lever is used to retract the pin. The indexing plunger remains unlocked as long as the handle is positioned over the dead-centre of the cam.
The ergonomic cam lever enables light handling with low effort.

Temperature range:

Permanent operating temperature acc. to IEC 216 max. 160°C.
Short-term operating temperature max. 250°C.

Advantages:

Simple and quick operation.
Suitable for high temperature applications.
With integrated detent function.

On request:

Special versions.

Accessory:

Spacer rings K0665
Positioning bushes for indexing plunger K1290
Mounting brackets K0638