

Rubber buffers steel or stainless steel, type A

Item description/product images



Description

Material:

Metal parts steel grade 5.6 or stainless steel.

Elastomer natural rubber, medium hardness, Shore 55A.

Version:

Steel electro zinc-plated.

Stainless steel bright.

Note:

The rubber buffers are widely-used construction elements for elastic mounting. They are used, among other things, as mountings for aggregates, motors, compressors, pumps and testing machinery.


Temperature range:

-30 °C to +80 °C

On request:

Other Shore grades.

Drawings



Overview of items

Rubber buffers, steel or stainless steel, type A

Order No.	Main material	D	G	L	H	Spring stiffness N/mm	Load N
K0566.00800855	steel	8	M3	6	8	24	31
K0566.01001055	steel	10	M4	10	10	35	32
K0566.01001555	steel	10	M4	10	15	50	50
K0566.01500855	steel	15	M4	10	8	130	104
K0566.01501055	steel	15	M4	10	10	122	122
K0566.01501555	steel	15	M4	10	15	59	88
K0566.02000855	steel	20	M6	18	8	725	580
K0566.02001055	steel	20	M6	18	10	300	300
K0566.02001555	steel	20	M6	18	15	200	300
K0566.02002055	steel	20	M6	18	20	133	332
K0566.02002555	steel	20	M6	18	25	90	270