

Drill bushes flanged DIN 172 Form B

Item description/product images




Description

Material:
Special steel.

Version:
Hardened and ground.
Hardness 740 ±80 HV 10

Note:
From diameter D1 over 15 mm size increases are 0.5 mm.

Drawings



Overview of items

Order No.	Form	D1	D2	D3	L1	Product type	L2	R	T1	T2
K1022.B0040X06	B	0,4	3	6	6	short	2	1	0,01	0,03
K1022.B0060X06	B	0,6	3	6	6	short	2	1	0,01	0,03
K1022.B0070X06	B	0,7	3	6	6	short	2	1	0,01	0,03
K1022.B0080X06	B	0,8	3	6	6	short	2	1	0,01	0,03
K1022.B0090X06	B	0,9	3	6	6	short	2	1	0,01	0,03
K1022.B0090X09	B	0,9	3	6	9	medium	2	1	0,01	0,03
K1022.B0100X06	B	1	3	6	6	short	2	1	0,01	0,03
K1022.B0100X09	B	1	3	6	9	medium	2	1	0,01	0,03
K1022.B0110X06	B	1,1	4	7	6	short	2	1	0,01	0,03
K1022.B0110X09	B	1,1	4	7	9	medium	2	1	0,01	0,03
K1022.B0120X06	B	1,2	4	7	6	short	2	1	0,01	0,03
K1022.B0120X09	B	1,2	4	7	9	medium	2	1	0,01	0,03
K1022.B0130X06	B	1,3	4	7	6	short	2	1	0,01	0,03
K1022.B0130X09	B	1,3	4	7	9	medium	2	1	0,01	0,03
K1022.B0140X06	B	1,4	4	7	6	short	2	1	0,01	0,03
K1022.B0140X09	B	1,4	4	7	9	medium	2	1	0,01	0,03