

Socket head screws full thread, DIN 912

Item description/product images



Description

Material:

Steel, stainless steel A2 or stainless steel A4.


Version:

Steel grade 8.8, bright (blackened) or electro zinc-plated.

Stainless steel A2-70, bright

Stainless steel A4-70, bright

Drawings



Overview of items

Order No.	Main material	Grade	Surface finish body	D	L	DK	K	SW
K1159.05X40	steel	8.8	bright (black)	M5	40	8,5	5	4
K1159.05X50	steel	8.8	bright (black)	M5	50	8,5	5	4
K1159.05X60	steel	8.8	bright (black)	M5	60	8,5	5	4
K1159.05X80	steel	8.8	bright (black)	M5	80	8,5	5	4
K1159.06X40	steel	8.8	bright (black)	M6	40	10	6	5
K1159.06X50	steel	8.8	bright (black)	M6	50	10	6	5
K1159.06X60	steel	8.8	bright (black)	M6	60	10	6	5
K1159.06X70	steel	8.8	bright (black)	M6	70	10	6	5
K1159.06X90	steel	8.8	bright (black)	M6	90	10	6	5
K1159.06X100	steel	8.8	bright (black)	M6	100	10	6	5
K1159.08X50	steel	8.8	bright (black)	M8	50	13	8	6
K1159.08X60	steel	8.8	bright (black)	M8	60	13	8	6
K1159.08X70	steel	8.8	bright (black)	M8	70	13	8	6
K1159.08X80	steel	8.8	bright (black)	M8	80	13	8	6
K1159.08X90	steel	8.8	bright (black)	M8	90	13	8	6
K1159.10X50	steel	8.8	bright (black)	M10	50	16	10	8
K1159.10X60	steel	8.8	bright (black)	M10	60	16	10	8
K1159.10X70	steel	8.8	bright (black)	M10	70	16	10	8
K1159.10X80	steel	8.8	bright (black)	M10	80	16	10	8
K1159.10X90	steel	8.8	bright (black)	M10	90	16	10	8
K1159.10X100	steel	8.8	bright (black)	M10	100	16	10	8
K1159.12X80	steel	8.8	bright (black)	M12	80	18	12	10
K1159.12X90	steel	8.8	bright (black)	M12	90	18	12	10
K1159.12X100	steel	8.8	bright (black)	M12	100	18	12	10
K1159.405X40	steel	8.8	galvanised	M5	40	8,5	5	4
K1159.405X70	steel	8.8	galvanised	M5	70	8,5	5	4
K1159.405X80	steel	8.8	galvanised	M5	80	8,5	5	4
K1159.406X40	steel	8.8	galvanised	M6	40	10	6	5
K1159.406X50	steel	8.8	galvanised	M6	50	10	6	5
K1159.406X60	steel	8.8	galvanised	M6	60	10	6	5
K1159.406X70	steel	8.8	galvanised	M6	70	10	6	5
K1159.406X80	steel	8.8	galvanised	M6	80	10	6	5