


## Thrust Washer (Form T)



## Order key

Type

Dimensions [mm]

G T M-04 08-005

iglidur® material

Form T

Metric

Inner-Ø d1

Outer-Ø d2

Thickness s



Dimensions according to ISO 3547-1  
and special dimensions



Imperial dimensions available

► From page 1445

## Dimensions [mm]

d1	d2	s	d4	d5	h	d6	Part No.
+0.25	-0.25	-0.05	-0.12 +0.12	+0.375 +0.125	+0.2 -0.2	+0.12	
4.0	8.0	0.5	4)	4)	0.2	8.0	GTM-0408-005
4.0	9.0	0.6	4)	4)	0.3	9.0	GTM-0409-006
4.0	9.0	1.6	4)	4)	0.3	9.0	GTM-0409-016
4.0	10.0	0.5	4)	4)	0.2	10.0	GTM-0410-005
4.0	11.0	0.5 (-0.06)	4)	4)	0.2	11.0	GTM-0411-005
5.0	9.5	0.6	4)	4)	0.3	9.5	GTM-0509-006
6.0	11.0	1.0	4)	4)	0.7	11.0	GTM-0611-010
6.0	12.0	1.5	4)	4)	1.0	12.0	GTM-0612-015
6.0	15.0	1.5	4)	4)	1.0	15.0	GTM-0615-015
6.0	20.0	1.5	13.0	1.5	1.0	20.0	GTM-0620-015
7.0	12.0	0.5	4)	4)	0.2	12.0	GTM-0712-005
7.0	13.0	0.5	4)	4)	0.2	13.0	GTM-0713-005
8.0	15.0	0.5	4)	4)	0.2	15.0	GTM-0815-005
8.0	15.0	1.5	4)	4)	1.0	15.0	GTM-0815-015
8.0	18.0	1.0	4)	4)	0.7	18.0	GTM-0818-010
8.0	18.0	1.5	13.0	1.5	1.0	18.0	GTM-0818-015
8.0	18.0	2.0	4)	4)	1.5	18.0	GTM-0818-020
9.0	13.0	1.0	4)	4)	0.7	13.0	GTM-0913-010
9.0	18.0	1.5	13.5	1.5	1.0	18.0	GTM-0918-015
10.0	17.8	0.5	4)	4)	0.2	17.8	GTM-1018-005
10.0	18.0	1.0	4)	4)	0.7	18.0	GTM-1018-010
10.0	18.0	1.5	4)	4)	1.0	18.0	GTM-1018-015
10.0	18.0	2.0	4)	4)	1.5	18.0	GTM-1018-020
10.0	20.0	1.5	4)	4)	0.7	20.0	GTM-1020-015
11.0	15.0	1.0	4)	4)	0.7	15.0	GTM-1115-010
11.0	27.0	0.5	4)	4)	0.2	27.0	GTM-1127-005
12.0	24.0	1.5	18.0	1.5	1.0	24.0	GTM-1224-015
12.2	30.0	1.5	4)	4)	1.0	30.0	GTM-1230-015

4) Design without fixing bore