


KAF

レベルアジャスター(アンカータイプ)

標準 在庫品 **RoHS** **SUS**

IMAO



タイプ	パッド	ネジ	ナット
KAF	SPCC 垂鉛三価クロメート	SS400 垂鉛三価クロメート	SS400 垂鉛三価クロメート
KAF-SUS	SUS304 酸化(不動態)皮膜	SUS304 酸化(不動態)皮膜	SUS304

スチール製		SUS製		M	L	L ₁	T	W	A	許容荷重 (kN)	質量 (g)
品番	価格	品番	価格								
KAF75-12×050	470	—	—	M12×1.75	75	50	8	19	3.5	5	200
KAF75-12×100	510	KAF75-12×100SUS	1,260		125	100					230
KAF75-12×120	520	KAF75-12×120SUS	1,370		145	120					245
KAF75-12×150	550	KAF75-12×150SUS	1,470		175	150					270
KAF75-16×065	590	—	—	M16×2	92	65	10	24	4	5	290
KAF75-16×100	670	KAF75-16×100SUS	1,890		127	100					330
KAF75-16×130	700	KAF75-16×130SUS	2,100		157	130					370
KAF75-16×150	720	KAF75-16×150SUS	1,890		177	150					400
KAF75-16×180	760	KAF75-16×180SUS	2,100		207	180					440
KAF75-16×200	780	—	—	M20×2.5	227	200	13	30	5	5	460
KAF75-20×100	860	KAF75-20×100SUS	2,700		130	100					510
KAF75-20×130	920	KAF75-20×130SUS	2,900		160	130					570
KAF75-20×150	960	KAF75-20×150SUS	3,100		180	150					620
KAF75-20×180	1,040	KAF75-20×180SUS	3,300	210	180	680					
KAF75-20×200	1,160	KAF75-20×200SUS	3,500	230	200	710					