

RENY

マイクロネジ Micro screw

外観に黒点(スラッジ)が入ることがありますが性能には影響ありません。

ネジ先端部のゲート残りは長さ(L)に対して5%以下です。

- ・表中の数値は参考値であり保証値ではありません。
- ・締付にはトルクドライバー及びトルクレンチをご使用ください。推奨締付トルクは使用状態における破断トルク値の50%です。
- ・耐熱性、耐薬品性は使用条件により変化しますので、必ず事前に使用状態でのテストを行ってください。
- ・ロット、各種条件により若干変色することがあります。
- ・在庫サイズ、形状及び使用材料メーカーは予告なく変更することがあります。

Black spots may occasionally appear on the external surface. However, this has no impact on performance.

Gate residue of screw head is 5% or less for length (L).

- ・ Values in the table are for reference purpose only, and they are not guaranteed values.
- ・ Please use torque driver or torque wrench for fastening. Recommended fastening torque is 50% of the torsional rupture torque.
- ・ Since heat resistance and chemical resistance change based on usage conditions, please test under actual usage conditions beforehand.
- ・ Discoloration may occur depending on lot and various conditions.
- ・ Sizes, shapes and manufacturers of raw materials may change without notice.

ORDER ▶ 品番・サイズ・販売単位にてご注文ください **RoHS compliant**

Please order by part number, size, and unit volume increment.

RENY/MPH


ガラス繊維強化ポリアミドMXD6 /
マイクロ(+)
Glass-fiber-reinforced polyamideMXD6 /
Micro cross recessed pan head screw



品番 Part number **RENY-MPH^(M-L)**

▶ **ねじり破断トルク**
Torsional rupture torque
単位/Unit M1.2 M1.4 M1.6
N・m 0.018 0.018 0.023

▶ **引張破断荷重**
Tensile rupture force
単位/Unit M1.2 M1.4 M1.6
N 80.9 61.4 54.1



※0番1種形状
Type1-Driver size #0

M	M1.2	M1.4	M1.6
ピッチ / Pitch	0.25	0.3	0.35
D×H	1.8×0.5	2×0.5	2.3×0.5
L	1.5	100	—
	1.8	100	—
	2	100	100
	2.5	100	100
	3	100	100
	3.5	100	100
	4	100	100
	6	—	100

販売単位 Quantity

RENY/MFH


ガラス繊維強化ポリアミドMXD6 /
マイクロ(+)
Glass-fiber-reinforced polyamideMXD6 /
Micro cross recessed flat head screw



品番 Part number **RENY-MFH^(M-L)**

▶ **ねじり破断トルク**
Torsional rupture torque
単位/Unit M1.2 M1.4 M1.6
N・m 0.022 0.039 0.056

▶ **引張破断荷重**
Tensile rupture force
単位/Unit M1.2 M1.4 M1.6
N 98.5 127.7 127.7



※0番1種形状
Type1-Driver size #0

M	M1.2	M1.4	M1.6
ピッチ / Pitch	0.25	0.3	0.35
D	2.3	2.5	2.8
L	2.5	100	100
	4	100	100

販売単位 Quantity