

K標準ピニオンギヤ〈モジュール3〉




●ご注文No.表記例

M3B20

ピニオンギヤNo.

M4B20

ピニオンギヤNo.



S1形状

m 機械構造用炭素鋼

s 黒染

〈M3〉

ピニオンギヤNo.	歯数	歯先円直径 Do	基準円直径 Dp	穴径 d H7	ボス径 BD	歯巾 T	全長 BL	形状	質量 (kg)	¥	Semi-F ¥
M 3 B 12	12	42	36	15	28				0.25	980	2,450
M 3 B 13	13	45	39	15	30				0.30	1,090	2,580
M 3 B 14	14	48	42	15	32	30	45	S1	0.35	1,140	2,620
M 3 B 15	15	51	45	15	36				0.40	1,320	2,830
M 3 B 16	16	54	48	15	38				0.50	1,350	3,120
M 3 B 17	17	57	51	15	39				0.65	1,390	3,180
M 3 B 18	18	60	54	15	40				0.67	1,570	3,380
M 3 B 19	19	63	57	15	45	30	45	S1	0.73	1,580	3,400
M 3 B 20	20	66	60	15	50				0.80	1,680	3,500
M 3 B 21	21	69	63	15	52				1.0	1,820	3,700
M 3 B 22	22	72	66	15	54				1.1	1,940	4,250
M 3 B 23	23	75	69	15	56				1.1	2,070	4,400
M 3 B 24	24	78	72	15	58	30	45	S1	1.2	2,110	4,450
M 3 B 25	25	81	75	20	60				1.3	2,270	4,600
M 3 B 26	26	84	78	20	65				1.5	2,430	4,800
M 3 B 27	27	87	81	20	65				1.6	2,550	4,950
M 3 B 28	28	90	84	20	70				1.7	2,620	5,650
M 3 B 29	29	93	87	20	70	30	45	S1	1.7	2,650	5,700
M 3 B 30	30	96	90	20	75				1.8	2,740	6,150
M 3 B 32	32	102	96	20	75				2.1	3,180	6,650
M 3 B 34	34	108	102	20	80				2.4	3,570	7,100
M 3 B 35	35	111	105	20	80				2.5	3,600	7,150
M 3 B 36	36	114	108	20	80	30	45	S1	2.6	3,640	7,200
M 3 B 38	38	120	114	25	80				3.0	4,120	7,750
M 3 B 40	40	126	120	25	80				3.1	4,160	7,780



ご注文方法

ピニオンギヤNo. と数量



ご案内

*ご要望に応じて、カタログ以外のサイズの製作、軸穴・キー・タップ等の加工をいたしますので詳細については弊社営業所までお問い合わせ下さい。



当日発送

納期