


鑄鉄製カートリッジ形ユニット

UCC形

円筒穴形，止ねじ式



軸径 12～60mm

軸径 mm	ユニット の呼び番号	寸 法 mm					軸 呼び番号	受 基本動 定格荷重 kN C_r	基本静 定格荷重 kN C_{or}	軸受箱の 呼び番号	ユニット 質 量 kg (参考)
		H	A	r	B	S					
12	UCC201	72	20	2	31	12.7	UC201D1	12.8	6.65	C204	0.5
15	UCC202	72	20	2	31	12.7	UC202D1	12.8	6.65	C204	0.5
17	UCC203	72	20	2	31	12.7	UC203D1	12.8	6.65	C204	0.5
20	UCC204	72	20	2	31	12.7	UC204D1	12.8	6.65	C204	0.5
25	UCC205	80	22	2	34.1	14.3	UC205D1	14.0	7.85	C205	0.6
	UCCX05	90	27	2	38.1	15.9	UCX05D1	19.5	11.3	CX05	1.1
	UCC305	90	26	2.5	38	15	UC305D1	21.2	10.9	C305	1.0
30	UCC206	85	27	2	38.1	15.9	UC206D1	19.5	11.3	C206	0.8
	UCCX06	100	30	2.5	42.9	17.5	UCX06D1	25.7	15.3	CX06	1.6
	UCC306	100	28	2.5	43	17	UC306D1	26.7	15.0	C306	1.3
35	UCC207	90	28	2	42.9	17.5	UC207D1	25.7	15.3	C207	0.9
	UCCX07	110	34	2.5	49.2	19	UCX07D1	29.1	17.8	CX07	1.8
	UCC307	110	32	3	48	19	UC307D1	33.5	19.1	C307	1.7
40	UCC208	100	30	2.5	49.2	19	UC208D1	29.1	17.8	C208	1.2
	UCCX08	120	38	2.5	49.2	19	UCX08D1	32.5	20.4	CX08	2.5
	UCC308	120	34	3	52	19	UC308D1	40.5	24.0	C308	2.1
45	UCC209	110	31	2.5	49.2	19	UC209D1	32.5	20.4	C209	1.5
	UCCX09	120	38	2.5	51.6	19	UCX09D1	35.0	23.2	CX09	2.2
	UCC309	130	38	3.5	57	22	UC309D1	53.0	32.0	C309	2.7
50	UCC210	120	33	2.5	51.6	19	UC210D1	35.0	23.2	C210	1.9
	UCCX10	130	40	2.5	55.6	22.2	UCX10D1	43.5	29.2	CX10	2.7
	UCC310	140	40	3.5	61	22	UC310D1	62.0	38.5	C310	3.3
55	UCC211	125	35	2.5	55.6	22.2	UC211D1	43.5	29.2	C211	2.1
	UCCX11	150	42	3	65.1	25.4	UCX11D1	52.5	36.0	CX11	4.1
	UCC311	150	44	3.5	66	25	UC311D1	71.5	45.0	C311	4.0
60	UCC212	130	38	2.5	65.1	25.4	UC212D1	52.5	36.0	C212	2.5
	UCCX12	160	44	3	65.1	25.4	UCX12D1	57.5	40.0	CX12	3.9
	UCC312	160	46	3.5	71	26	UC312D1	82.0	52.0	C312	4.8

備考1. ユニットの呼び番号は無給油式を示し，給油式の場合には呼び番号の後に記号 "D1" が付く。