

溶接式異径ヘルール／溶接式異径偏心ヘルール


Reducing Ferrule for Welding／Reducing Ferrule (Eccentric) for Welding

溶接式異径ヘルール

Type CLF-WX

Reducing Ferrule for Welding

機械加工仕上：内面 ($Ra \leq 0.8\mu m$)
Machined finish : internal surface ($Ra \leq 0.8\mu m$)




※SUS316Lのみ Only SUS316L
※※SUS304のみ Only SUS304

Nom.size	OD	ID1	ID2	A	L	Mass kg
※ 1.0 ^S ×8A	13.8	10.5	23	50.5	21.5	0.090
※ 1.0 ^S ×10A	17.3	14	23	50.5	21.5	0.089
※ 1.0 ^S ×15A	21.7	17.5	23	50.5	21.5	0.090
※ 1.5 ^S ×8A	13.8	10.5	35.7	50.5	21.5	0.076
※ 1.5 ^S ×10A	17.3	14	35.7	50.5	21.5	0.075
※ 1.5 ^S ×15A	21.7	17.5	35.7	50.5	21.5	0.078
1.5 ^S ×1.0 ^S	25.4	23	35.7	50.5	21.5	0.059
1.5 ^S ×1.25 ^S	31.8	29.4	35.7	50.5	21.5	0.060
※ 2.0 ^S ×15A	21.7	17.5	47.8	64	21.5	0.119
2.0 ^S ×1.0 ^S	25.4	23	47.8	64	21.5	0.108
2.0 ^S ×1.25 ^S	31.8	29.4	47.8	64	21.5	0.105
2.0 ^S ×1.5 ^S	38.1	35.7	47.8	64	21.5	0.095
2.5 ^S ×1.5 ^S	38.1	35.7	59.5	77.5	21.5	0.156
2.5 ^S ×2.0 ^S	50.8	47.8	59.5	77.5	21.5	0.142
3.0 ^S ×1.5 ^S	38.1	35.7	72.3	91	21.5	0.204
3.0 ^S ×2.0 ^S	50.8	47.8	72.3	91	21.5	0.207
3.0 ^S ×2.5 ^S	63.5	59.5	72.3	91	21.5	0.187
※※ 4.0 ^S ×1.5 ^S	38.1	35.7	97.6	119	28	0.445
※※ 4.0 ^S ×2.0 ^S	50.8	47.8	97.6	119	28	0.436
※※ 4.0 ^S ×2.5 ^S	63.5	59.5	97.6	119	28	0.421
※※ 4.0 ^S ×3.0 ^S	76.3	72.3	97.6	119	28	0.385

溶接式異径偏心ヘルール

Type CLF-WXE

Reducing Ferrule for Welding



機械加工仕上：内面 ($Ra \leq 0.8\mu m$)
Machined finish : internal surface ($Ra \leq 0.8\mu m$)

Nom.size	OD	ID1	ID2	A	L	Mass kg
1.5 ^S ×1.0 ^S	25.4	23	35.7	50.5	21.5	0.090
2.0 ^S ×1.0 ^S	25.4	23	47.8	64	21.5	0.170
2.0 ^S ×1.5 ^S	38.1	35.7	47.8	64	21.5	0.138
2.5 ^S ×1.5 ^S	38.1	35.7	59.5	77.5	21.5	0.232
2.5 ^S ×2.0 ^S	50.8	47.8	59.5	77.5	21.5	0.179
3.0 ^S ×2.0 ^S	50.8	47.8	72.3	91	21.5	—
3.0 ^S ×2.5 ^S	63.5	59.5	72.3	91	21.5	—