


溶接式89°エルボ／溶接式91°エルボ  
89° Elbow both end Weld／91° Elbow both end Weld

溶接式 89° エルボ  
Type 89EL-W

89° Elbow both end Weld




※すべてSUS316L  
All SUS316L

Nom.size	OD	t	A	Mass kg
1.0 <sup>S</sup>	25.4	1.2	33.5	0.04
1.5 <sup>S</sup>	38.1	1.2	48.5	0.09
2.0 <sup>S</sup>	50.8	1.5	60.5	0.18
2.5 <sup>S</sup>	63.5	2.0	83.5	0.41
3.0 <sup>S</sup>	76.3	2.0	88.5	0.47
8A	13.8	1.65	38	0.03
10A	17.3	1.65	38	0.036
15A	21.7	2.1	38	0.062

溶接式 91° エルボ  
Type 91EL-W

91° Elbow both end Weld



※すべてSUS316L  
All SUS316L

Nom.size	OD	t	A	Mass kg
1.0 <sup>S</sup>	25.4	1.2	33.5	0.04
1.5 <sup>S</sup>	38.1	1.2	48.5	0.09
2.0 <sup>S</sup>	50.8	1.5	60.5	0.18
2.5 <sup>S</sup>	63.5	2.0	83.5	0.41
3.0 <sup>S</sup>	76.3	2.0	88.5	0.47
8A	13.8	1.65	38	0.03
10A	17.3	1.65	38	0.036
15A	21.7	2.1	38	0.062