

### ③ サニタリー継手

## 配管サポート及び工具


Piping Support and Tools

パイプハンガ/小口径パイプハンガ/一般配管用ハンガ  
Pipe Hanger/Small Dia. Pipe Hanger/General Piping Hanger

### パイプハンガ

Pipe Hanger

#### Type PHG-M




Nom.size	D	A	B	C	E	Mass kg
1.0 <sup>S</sup>	25.4	49.7	40.5	28	24	0.108
1.25 <sup>S</sup>	31.8	56.2	44	28	24	0.114
1.5 <sup>S</sup>	38.1	62.8	47	28	24	0.120
2.0 <sup>S</sup>	50.8	79.1	53.5	32	24	0.161
2.5 <sup>S</sup>	63.5	93.8	60	32	24	0.177
3.0 <sup>S</sup>	76.3	107.7	67.5	32	24	0.195
3.5 <sup>S</sup>	89.1	122.5	74	32	24	0.215
4.0 <sup>S</sup>	101.6	135.1	80	32	24	0.231

### パイプハンガ

Pipe Hanger

#### Type PHG-L




Nom.size	D	A	B	C	E	Mass kg
4.5 <sup>S</sup>	114.3	172	84	30	24	0.371
5.5 <sup>S</sup>	139.8	198	97	30	24	0.422
6.5 <sup>S</sup>	165.2	222	109.5	30	24	0.475

### 小口径パイプハンガ

Small Dia. Pipe Hanger

#### Type PHG-S




Nom.size	D	A	B	C	E	Mass kg
8A	13.8	56	25	14	11.7	0.062
10A	17.3	56	25	14	11.7	0.057
15A	21.7	56	25	14	11.7	0.050

### 小口径パイプハンガ

Small Dia. Pipe Hanger

#### Type PHG-AH




Nom.size	D	A	B	C	E	Mass kg
8A	13.8	56	30	18	12	0.118
10A	17.3	56	30	18	12	0.115
15A	21.7	56	30	18	12	0.107

### 一般配管用ハンガ

General Piping Hanger

#### Type PHG-BH



※オプション: スリーブ(フィルター入り PTFE)  
Option: Sleeve(PTFE Filler)

Nom.size	D	A	B	C	E	Mass kg
20A	27.2	75	35	26	15	0.245
25A	34.0	75	40	26	15	0.243
32A	42.7	85	49	26	18	0.285
40A	48.6	92	52	26	18	0.311
50A	60.5	106	58	26	18	0.360

写真は3DCGです。