

Spring Plungers • headed, with ball and slot

EH 22050.



Product Description

Spring plungers can be used for locating or for applying pressure, as a detent or for ejection. Precise screwing depth due to head.

Material

Body

- Free cutting steel, blackened
- Stainless steel 1.4305

Ball

- Ball-bearing steel, hardened
- Stainless steel, hardened


Spring

- stainless steel


Assembly

Respect dimension l_3 for M 4 / M 5.

Characteristic



Standard spring load



Heavy spring load

More information


Notes

Special types on request.
Spring plungers are specially tested for spring range and forces.


References

Thread lock on request, please refer to appendix - Technical Data -
Calculation of indexing resistance, please refer to appendix - Technical Data -

Drawing





Size M4+M5



Size M6-M12

Order information

Dimensions							Stroke s	Spring load ¹⁾				Art. No.
d ₁	d ₂	d ₃	l ₁	l ₂	l ₃ min.	n		F ₁ ~	F ₂ ~	max.		
[mm]							[mm]	[N]		[°C]	[g]	
free cutting steel, standard spring load												
M 4	2.5	6	9.5	6.5	5.0	0.6	0.8	8.0	14.0	250	1.0	22050.0930
M 5	3.0	8	12.5	8.5	6.7	0.8	0.9	8.0	14.0	250	2.2	22050.0931
M 6	3.5	10	14.0	9.0	–	1.0	1.0	11.0	18.0	250	3.7	22050.0932
M 8	4.5	13	16.5	11.0	–	1.2	1.5	18.0	31.0	250	7.4	22050.0933
M10	6.0	16	20.0	14.0	–	1.5	2.0	24.0	45.0	250	13.0	22050.0934
M12	8.0	18	22.0	15.0	–	2.0	2.5	26.0	49.0	250	19.0	22050.0935

¹⁾ statistical average value