

## Ball Lock Pins • self-locking, with combination handle

EH 22370.



## Product Description

For quick fastening, locking, adjusting, changing and securing. Quickly and easily unlockable for frequently repeated connections.

All versions are corrosion resistant.

Ergonomic grip, different colour combinations available. The grip design provides protection of unintentional unlocking.

## Material

## Pin part

- Stainless steel 1.4305

## Handle

- Thermoplastic PA 6 grey / orange
- Thermoplastic PA 6 grey / grey
- Thermoplastic PA 6 grey / blue
- Thermoplastic PA 6 black / black

## Spring

- stainless steel

## Operation

The balls are unlocked by pressing the button.

## More information

## Notes

Special types on request.

## References

Stainless steel 1.4542, see EH 22380.


## Accessories

Can easily be fitted with retaining cable EH 22400.



## Further products

- Ball Lock Pins, self-locking, with combination handle, precipitation-hardened
- Locating Bushings, for ball lock pins and socket pins
- Locating Bushings, with flange, for ball lock pins and socket pins
- Retaining Cables
- Positioning Bushings, with collar, DIN 172 A
- Positioning Bushings, without collar, DIN 179 A

## Drawing



## Order information

Dimensions								Location hole H11	Shearing resistance, two-shear <sup>1)</sup> min.	 min.   max.	 [g]	Art. No.	
d <sub>1</sub> -0.04 -0.08	l <sub>1</sub> +0.6	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	l <sub>2</sub> ±1	l <sub>3</sub>	l <sub>4</sub>						
[mm]								[mm]	[kN]	[°C]	[g]		
Handle colour: orange													
5	10	5.5	33.2	14.5	6.0	26.7	10.8	5	14	-30	80	21.0	<a href="#">22370.0152</a>
5	15	5.5	33.2	14.5	6.0	26.7	10.8	5	14	-30	80	15.0	<a href="#">22370.0153</a>
5	20	5.5	33.2	14.5	6.0	26.7	10.8	5	14	-30	80	16.0	<a href="#">22370.0154</a>
5	25	5.5	33.2	14.5	6.0	26.7	10.8	5	14	-30	80	17.0	<a href="#">22370.0155</a>
5	30	5.5	33.2	14.5	6.0	26.7	10.8	5	14	-30	80	18.0	<a href="#">22370.0156</a>
5	35	5.5	33.2	14.5	6.0	26.7	10.8	5	14	-30	80	19.0	<a href="#">22370.0145</a>

<sup>1)</sup> Shearing resistance similar to DIN 50141