

Mounting Pads • protected against slipping

EH 22590.



Product Description

Mounting pads can be used as foot or thrust pad. Not parallel bearing surfaces up to 15° degrees can be compensated.
The plastic cover on the mounting pad prevents slipping.

Material

Ball element

- Free cutting steel, induction-hardened, blackened.
- Stainless steel 1.4305

Ball element with bolt

- Heat-treated steel, blackened
- Stainless steel 1.4305

Rubber cap

- Rubber, black

Lock nut

- Steel, blackened, ISO 4032
- Steel, blackened, DIN 934
- Stainless Steel A2, ISO 4032
- Stainless Steel A2, DIN 934

Pad


- Heat-treated steel, tempered, blackened
- Stainless steel 1.4305
- Thermoplastic POM, white

More information

Notes

For the versions $d_1 = M10$ and $M12$ the lock nut conforms to DIN 934.

Drawing



picture 1

picture 2

Order information

| d_1 | l_1 | d_2 | Dimensions | | | | WS | Load capacity for static load max. | [g] | Art. No. |
|--|-------|-------|------------|-------|-------|-----|----|--|------|------------|
| | | | l_2 | h_1 | h_2 | t | | | | |
| [mm] | | | | | | | | | | |
| pad and ball element – picture 1, Heat-treated steel | | | | | | | | | | |
| M 6 | – | 22.5 | – | 16.5 | 6.4 | 5.0 | 10 | 10 | 19.0 | 22590.1006 |
| M 8 | – | 28.0 | – | 20.6 | 8.3 | 7.0 | 13 | 18 | 40.0 | 22590.1008 |
| M10 | – | 36.0 | – | 26.0 | 11.0 | 9.0 | 17 | 20 | 80.0 | 22590.1010 |