

Mounting Pads

EH 22590.



Product Description

Mounting pads can be used as foot or thrust pad. Not parallel bearing surfaces up to 15° degrees can be compensated.

Material

Ball element

- Heat-treated steel, tempered, blackened
- Stainless steel 1.4305

Ball element with bolt

- Heat-treated steel, tempered, blackened
- Stainless steel 1.4305

Lock nut

- Steel, blackened, ISO 4032
- Steel, blackened, DIN 934
- Stainless Steel A2, ISO 4032
- Stainless Steel A2, DIN 934

Pad


- Heat-treated steel, blackened
- Stainless steel 1.4305
- Thermoplastic POM, white

More information

Notes

For the versions $d_1 = M10$ and $M12$ the lock nut conforms to DIN 934.

Drawing



Order information

d ₁	l ₁	d ₂	Dimensions				t	WS	Load capacity for static load max.	Temperature		Weight [g]	Art. No.
			l ₂	h ₁	h ₂	min.				max.			
			[mm]						[kN]	[°C]			
pad and ball element – picture 1, Heat-treated steel													
M 6	–	20	–	14	2.5	5.0	10	10	–	250	15.0	22590.0006	
M 8	–	25	–	18	4.0	7.0	13	18	–	250	33.0	22590.0008	
M10	–	32	–	22	5.0	9.0	17	20	–	250	67.0	22590.0010	
M12	–	40	–	26	6.0	11.0	19	35	–	250	112.0	22590.0012	
M16	–	50	–	32	7.0	13.5	24	45	–	250	254.0	22590.0016	
M20	–	60	–	42	8.0	17.0	30	55	–	250	451.0	22590.0020	
M24	–	60	–	45	9.5	19.0	36	65	–	250	498.0	22590.0024	