

Locating Pins • with ball end

EH 22630.




Product Description

Ball ended locating pins facilitate easy inserting and removing avoiding clamping inclination.

Material

- Tool steel, hardened, blackened and ground
- Stainless steel 1.4305, ground, surface heat-treated

Drawing



Order information

Dimensions										Location hole D ₁ H7		Art. No.
d ₁ g6	d ₂ n6	d ₃ -0.01 -0.05	d ₄	l ₁	l ₂	l ₃	t	r	b	[mm]	[g]	
[mm]												
with ball end plain – picture 1, Tool steel												
10	7	10	M3	7	10	2.5	6	2.5	–	7	6.7	22630.0310
12	8	12	M4	8	12	3.0	8	3.0	–	8	11.0	22630.0312
16	12	16	M5	12	16	4.0	10	4.0	–	12	31.0	22630.0316
20	14	20	M5	14	20	5.0	10	5.0	–	14	58.0	22630.0320
22	16	22	M5	16	22	5.5	10	5.5	–	16	81.0	22630.0322
25	18	25	M5	18	25	6.0	10	6.0	–	18	118.0	22630.0325
with ball end plain – picture 1, stainless steel												
10	7	10	M3	7	10	2.5	6	2.5	–	7	7.0	22630.0350
12	8	12	M4	8	12	3.0	8	3.0	–	8	11.0	22630.0352
16	12	16	M5	12	16	4.0	10	4.0	–	12	30.0	22630.0356
20	14	20	M5	14	20	5.0	10	5.0	–	14	57.0	22630.0360