

Ball-Ended Thrust Screws • headed, round ball

EH 22710.



Product Description

Ball-ended thrust screws can also be used for positioning and clamping, tightening or supporting of non-parallel surfaces.

Material

Ball

- Ball-bearing steel, hardened
- Stainless steel, hardened

Screw

- Heat-treated steel, $1200 \pm 100 \text{ N/mm}^2$
- Stainless steel 1.4305

More information


Notes

Special types on request.

References

Thread lock on request, please refer to appendix - Technical Data -

Drawing



Order information

d ₁	l ₁ ~	Dimensions				ball diameter	WS [mm]	Load capacity for static load ¹⁾ max. [kN]	 [g]	Art. No.
		d ₂	l ₃	l ₄						
		[mm]								
round ball, Heat-treated steel										
M 6	20.8	10	6	3.0	4.0	5	9	6.1	22710.0062	
M 6	30.8	10	6	3.0	4.0	5	9	7.9	22710.0064	
M 6	40.8	10	6	16.0	4.0	5	9	9.9	22710.0066	
M 8	21.2	13	8	3.5	5.5	6	15	13.0	22710.0082	
M 8	36.2	13	8	3.5	5.5	6	15	17.0	22710.0084	
M 8	51.2	13	8	22.0	5.5	6	15	23.0	22710.0086	
M10	26.7	16	10	4.5	7.0	8	20	24.0	22710.0102	
M10	41.7	16	10	4.5	7.0	8	20	32.0	22710.0104	
M10	61.7	16	10	28.0	7.0	8	20	44.0	22710.0106	
M12	32.0	18	12	5.0	8.5	10	30	39.0	22710.0122	
M12	52.0	18	12	5.0	8.5	10	30	52.0	22710.0124	
M12	82.0	18	12	44.0	8.5	10	30	80.0	22710.0126	
M16	43.3	24	16	6.0	12.0	14	60	94.0	22710.0162	
M16	63.3	24	16	6.0	12.0	14	60	122.0	22710.0164	
M16	83.3	24	16	36.0	12.0	14	60	154.0	22710.0166	
M20	54.2	30	20	7.5	15.0	17	90	186.0	22710.0202	
M20	84.2	30	20	28.0	15.0	17	90	255.0	22710.0204	
M20	104.2	30	20	48.0	15.0	17	90	306.0	22710.0206	
M24	64.7	36	24	9.0	18.0	19	120	327.0	22710.0242	
M24	94.7	36	24	30.0	18.0	19	120	428.0	22710.0244	
M24	124.7	36	24	60.0	18.0	19	120	532.0	22710.0246	
round ball, stainless steel										
M 6	20.8	10	6	3.0	4.0	5	9	6.1	22710.0752	
M 6	30.8	10	6	3.0	4.0	5	9	7.9	22710.0754	
M 6	40.8	10	6	16.0	4.0	5	9	10.0	22710.0756	
M 8	21.2	13	8	3.5	5.5	6	15	13.0	22710.0762	
M 8	36.2	13	8	3.5	5.5	6	15	17.0	22710.0764	

¹⁾ Statements on load capacity are not valid for the stainless steel type.