

Pins  
EH 22690.

Product Description


To be used as seats, stops and thrust pads.

Material

- Steel, case-hardened, blackened



Drawing



Order information

h	d <sub>1</sub>	Dimensions				t	WS	Tightening torque max.	[g]	Art. No.
		d <sub>2</sub>	d <sub>3</sub>	l	[mm]					
with male thread, bearing surface plain – picture 1										
10 ± 0.01	M 8	19.4	17	10	–	17	18	21	22690.0021	
10 ± 0.01	M10	21.9	19	12	–	19	32	28	22690.0031	
15 ± 0.01	M10	21.9	19	12	–	19	32	40	22690.0032	
10 ± 0.01	M12	25.2	22	14	–	22	60	40	22690.0001	
15 ± 0.01	M12	25.2	22	14	–	22	60	55	22690.0002	
15 ± 0.01	M16	33.0	30	19	–	30	140	110	22690.0042	
20 ± 0.01	M16	33.0	30	19	–	30	140	140	22690.0043	
20 ± 0.01	M20	40.0	36	24	–	36	290	214	22690.0052	
25 ± 0.01	M20	40.0	36	24	–	36	290	257	22690.0053	
20 ± 0.01	M24	46.0	41	29	–	41	498	300	22690.0062	
25 ± 0.01	M24	46.0	41	29	–	41	498	356	22690.0063	
30 ± 0.01	M24	46.0	41	29	–	41	498	412	22690.0064	

<sup>1)</sup> The tightening torque of bolts with female thread is for threaded pins, quality 8. The bolt has to be tightened over the total thread length.