

Studs • DIN 6379 for T-nuts EH 23040.



Product Description

Studs combined with T-nuts DIN 508 (EH 23010./23020.), fixture nuts DIN 6330 (EH 23070.) and plain washers DIN 6340 (EH 23060.) become complete clamping studs. These studs are characterised by the rolled thread.

Material

- Heat-treated steel

More information


References

For torques and strengths please refer to appendix - Technical Data - Studs with elongated dimension b_1 also available.

Further products

- Nuts for T-Slots, DIN 508
- Studs, DIN 6379 b_1 long for nut for T-Slots
- Studs, with internal hexagon, similar to DIN 6379, for nuts for T-Slots
- Shaft / Plain Washers, DIN 6340 heat-treated
- Fixture Nuts, DIN 6330 (height 1,5 d)

Drawing



Order information

d	l	Dimensions		b ₂	g	Art. No.
		b ₁	[mm]			
quality 10.9						
M 6	32	9		16	5.3 g	23040.0061 ¹⁾
M 6	50	9		30	8.4 g	23040.0062
M 6	63	9		40	11.0 g	23040.0064 ¹⁾
M 6	80	9		50	13.0 g	23040.0063
M 8	40	11		20	12.0 g	23040.0081
M 8	63	11		40	19.0 g	23040.0082
M 8	100	11		63	31.0 g	23040.0083
M 8	160	11		100	49.0 g	23040.0084 ¹⁾
M10	50	13		25	24.0 g	23040.0101
M10	80	13		50	39.0 g	23040.0102
M10	100	13		75	50.0 g	23040.0106 ¹⁾
M10	125	13		75	61.0 g	23040.0103
M10	160	13		100	78.0 g	23040.0105 ¹⁾
M10	200	13		122 ²⁾	98.0 g	23040.0104
M12	50	15		25	35.0 g	23040.0121
M12	63	15		32	44.0 g	23040.0122 ¹⁾
M12	80	15		50	56.0 g	23040.0123

¹⁾ DIN standards do not include these dimensions.

²⁾ Dimension differ from DIN standard.