

## Studs • DIN 6379 b1 long for nut for T-Slots EH 23040.



### Product Description

Studs combined with T-nuts DIN 508 (EH 23010./23020.), fixture nuts DIN 6330 (EH 23070.) and plain washers DIN 6340 (EH 23060.) become complete clamping studs. These studs are characterised by the rolled thread.

### Material

- Heat-treated steel

### More information


### References

For torques and strengths please refer to appendix - Technical Data -

### Further products

- Nuts for T-Slots, DIN 508
- Studs, DIN 6379 for T-nuts
- Studs, with internal hexagon, similar to DIN 6379, for nuts for T-Slots
- Shaft / Plain Washers, DIN 6340 heat-treated
- Fixture Nuts, DIN 6330 (height 1,5 d)

### Drawing



### Order information

d	Dimensions		b <sub>1</sub>	b <sub>2</sub>	g	Art. No.
	l	[mm]				
<b>quality 10.9</b>						
M 6	50		15	30	8.4	23040.0562
M 6	63		15	40	11.0	23040.0563
M 6	80		15	50	14.0	23040.0564
M 8	63		20	40	19.0	23040.0582
M 8	100		20	63	31.0	23040.0583
M 8	160		20	100	49.0	23040.0584
M10	80		25	50	39.0	23040.0602
M10	100		25	75	49.0	23040.0603
M10	125		25	75	61.0	23040.0604
M10	160		25	100	78.0	23040.0605 <sup>1)</sup>
M10	200		25	122	98.0	23040.0606
M12	63 <sup>2)</sup>		–	–	44.0	23040.0622
M12	80 <sup>2)</sup>		–	–	56.0	23040.0623
M12	100		30	63	71.0	23040.0624 <sup>1)</sup>
M12	125		30	75	88.0	23040.0625
M12	160		30	100	112.0	23040.0626
M12	200		30	122	140.0	23040.0627
<b>quality 8.8</b>						
M16	80 <sup>2)</sup>		–	–	100.0	23040.0662
M16	125		40	63	161.0	23040.0664
M16	160		40	75	207.0	23040.0665
M16	200		40	100	260.0	23040.0666 <sup>1)</sup>
M16	250		40	125	325.0	23040.0667

<sup>1)</sup> DIN standards do not include these dimensions.

<sup>2)</sup> Throughgoing thread