

Eccentric Quick Clamps • with screw

EH 23390.



Product Description

For quick and easy clamping and releasing of workpieces.
When using the "adjustable" design (picture 2) the lever position can be moved.

Material

Support washer

- Thermoplastic PA, glass-fiber reinforced
- Thermoplastic POM, glass-fiber reinforced

Lever

- Zinc die-cast, plastic coated, black, similar to RAL 9005

Inner parts

- Steel, zinc-plated by galvanization
- Stainless steel 1.4305


Screw

- Steel, zinc-plated by galvanization
- Stainless steel 1.4305

Adjusting nut

- Steel, zinc-plated by galvanization
- Stainless steel 1.4305

Drawing



Order information

Dimensions									Stroke s at 90° lever position	 max.		Art. No.
l	d ₂	h ₁ max. in clamping position	d ₃	d ₄	d ₅	h ₂ max.	Regulating- range h ₃ min.	b				
[mm]									[mm]	[°C]	[g]	
with screw – picture 1, steel												
63	M5	16	16	–	18.5	16.4	–	16	0.75	80	62	23390.0030
63	M5	20	16	–	18.5	16.4	–	16	0.75	80	63	23390.0031
63	M5	25	16	–	18.5	16.4	–	16	0.75	80	63	23390.0032
63	M5	30	16	–	18.5	16.4	–	16	0.75	80	65	23390.0033
63	M5	35	16	–	18.5	16.4	–	16	0.75	80	65	23390.0034
63	M5	40	16	–	18.5	16.4	–	16	0.75	80	65	23390.0035
63	M5	50	16	–	18.5	16.4	–	16	0.75	80	67	23390.0036
63	M6	16	16	–	18.5	16.4	–	16	0.75	80	63	23390.0009
63	M6	20	16	–	18.5	16.4	–	16	0.75	80	65	23390.0010
63	M6	25	16	–	18.5	16.4	–	16	0.75	80	65	23390.0011
63	M6	30	16	–	18.5	16.4	–	16	0.75	80	65	23390.0012
63	M6	35	16	–	18.5	16.4	–	16	0.75	80	66	23390.0013