

Loose Slot Tenons • DIN 6323

EH 23120.

Product Description




To be used for locating fixtures and clamping elements onto machine tables with T-slots to DIN 650.

Being simply pushed into position after fixture or clamping element has been roughly positioned, they cannot cause damage to the machine as could protruding fixed slot tenons or low slot tenons.


Material

- Steel, case-hardened, blackened, ground

Drawing



Order information

T-slot size fixture b ₁ h6 [mm]	T-slot size machine b ₂ h6 [mm]	Dimensions					 [g]	Art. No.
		h ₁	h ₂	h ₃	h ₄	l		
		[mm]						
form A, b ₁ > b ₂ – picture 1								
12	10	12.0	3.6	–	–	20	20	23120.0010
20	12	14.0	5.5	–	–	32	52	23120.0012
20	14	14.0	5.5	–	–	32	56	23120.0014
20	16	14.0	5.5	–	–	32	61	23120.0016
20	18	14.0	5.5	–	–	32	65	23120.0018
form B, b ₁ = b ₂ – picture 2								
12	12	28.6	–	5.5	9	20	45	23120.0011
20	20	45.5	–	7.0	16	32	199	23120.0020
form C, b ₁ < b ₂ – picture 3								
20	22	50.5	–	7.0	18	40	305	23120.0022
20	28	61.5	–	7.0	24	40	472	23120.0028
20	36	76.5	–	7.0	30	50	952	23120.0036