

Bedding Supports EH 23220.

Product Description



The bedding support is used to **support** overdetermined clamping points on components. The benefits of the bedding support are:

- Support for unstable components, without distortion
- Eliminates tool vibration during machining
- Compact, low construction
- Supports ribs, beads and shackles, for reinforcement of clamped components
- Distortion-free support of raw parts
- Easy handling
- Flat and long design allows clamping with adjustable clamping lever even outside the workpiece.

Material

Handle

- Zinc die-cast

Clamp


- Steel, case-hardened, blackened, ground

Operation

1. By releasing the clamping lever, the support bolt contacts the workpiece with a light spring load.
2. By clamping the clamping lever, the support pin is blocked without displacement.
3. The clamping lever is released after removal of the workpiece. Then push the support pin into the starting position and clamp using the lever.

By screwing grub screws or supports into the support pin's female thread, the support height can be adjusted.

Drawing



Sizes 8,5 x 75, 13 x 150 and 17 x 170 have only one slot.

Order information

Dimensions														Stroke s	Load capacity max.	e	Art. No.		
b_3	l_1	l_2	l_3	l_4	l_5	l_6	l_7	b_1	b_2	d_1	d_2	h_1	h_2					r	[mm]
[mm]																			
8.5	75	35	13	-	13	62	5	30	10	M 8	13	19.5	11.5	-	3	0.5	24400.0311	342 g	23220.0085
13.0	150	90	20	-	17	74	-	50	25	M10	20	24.0	14.0	15	6	2.5	24400.0411	1379 g	23220.0150
17.0	170	100	25	-	27	108	11	60	20	M16	26	34.0	21.5	-	11	5.0	24400.0611	3 kg	23220.0170
13.0	300	100	30	160	17	74	-	50	25	M10	20	24.0	14.0	15	6	2.5	24400.0411	1900 g	23220.0300
25.0	387	110	30	200	30	89	-	85	40	M20	32	40.0	25.0	24	11	10.0	24420.0210	7 kg	23220.0450