

Adjustable Clamping Levers • with screw

EH 24400.

Product Description

Adjustable clamping levers find versatile applications when the area of use is confined or a specific lever position is required.

Material

Lever

- Zinc die-cast, plastic coated, orange similar to RAL 2004, matt structure
- Zinc die-cast, plastic coated, silver, similar to RAL 9006, matt structure
- Zinc die-cast, plastic coated, black, similar to RAL 9005, matt structure

Inner parts

- Steel, blackened, quality 5.8

Screw

- Steel, blackened, quality 5.8

Operation


By lifting the lever the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

More information


Notes

The screw part can be exchanged.

Drawing



Order information

Dimensions											Art. No.
d ₁	d ₂	l ₁	d ₃	h ₁ [mm]	h ₂	h ₃	h ₄	l ₂	[g]		
orange											
13	M 4	12	10.0	24.5	4.0	3.5	30.5	30	27.0	24400.0010	
13	M 4	16	10.0	24.5	4.0	3.5	30.5	30	27.0	24400.0014	
13	M 4	20	10.0	24.5	4.0	3.5	30.5	30	28.0	24400.0018	
13	M 4	25	10.0	24.5	4.0	3.5	30.5	30	28.0	24400.0022	
13	M 4	32	10.0	24.5	4.0	3.5	30.5	30	28.0	24400.0026	
14	M 5	12	10.0	24.5	4.0	3.0	35.0	45	36.0	24400.0041	
14	M 5	16	10.0	24.5	4.0	3.0	35.0	45	36.0	24400.0051	
14	M 5	20	10.0	24.5	4.0	3.0	35.0	45	37.0	24400.0061	
14	M 5	25	10.0	24.5	4.0	3.0	35.0	45	38.0	24400.0071	
14	M 5	32	10.0	24.5	4.0	3.0	35.0	45	38.0	24400.0081	
14	M 5	40	10.0	24.5	4.0	3.0	35.0	45	39.0	24400.0086	
14	M 6	12	10.0	24.5	4.0	3.0	35.0	45	37.0	24400.0131	
14	M 6	16	10.0	24.5	4.0	3.0	35.0	45	37.0	24400.0141	
14	M 6	20	10.0	24.5	4.0	3.0	35.0	45	39.0	24400.0151	
14	M 6	25	10.0	24.5	4.0	3.0	35.0	45	41.0	24400.0161	
14	M 6	32	10.0	24.5	4.0	3.0	35.0	45	40.0	24400.0171	
14	M 6	40	10.0	24.5	4.0	3.0	35.0	45	41.0	24400.0181	
14	M 6	50	10.0	24.5	4.0	3.0	35.0	45	3.1	24400.0191	